

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P789293

Luminaire Tested: LER6D10D010-EC6DR650210IC9027-6LBS1LI

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P789293  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D10D010-EC6DR650210IC9027-6LBS1LI  
Description: 6 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1701.4 lumens  
Efficiency: N/A  
Efficacy: 145.4 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96  
Luminous Opening: Circular (Dia: 0.48' x H: 0')  
CIE Type: Direct


Input Watts (W): 11.7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P789293  
CATALOG NUMBER: LER6D10D010-EC6DR650210IC9027-6LBS1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P789293

CATALOG NUMBER: LER6D10D010-EC6DR650210IC9027-6LBS1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93				93															
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85				85															
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78				78															
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72				72															
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66				66															
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61				61															
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56				56															
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52				52															
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49				49															
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46				46															

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	90228
5°	89998
10°	89924
15°	87147
20°	79337
25°	69139
30°	57505
35°	45567
40°	32883
45°	20773
50°	10831
55°	5753
60°	3025
65°	1658
70°	700
75°	767
80°	538
85°	469

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 20773 cd/sqm



TEST NUMBER: P789293

CATALOG NUMBER: LER6D10D010-EC6DR650210IC9027-6LBS1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	146.1	8.6
10°-20°	400.1	23.5
20°-30°	489.0	28.7
30°-40°	396.8	23.3
40°-50°	197.7	11.6
50°-60°	55.1	3.2
60°-70°	12.5	0.7
70°-80°	3.3	0.2
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1035.2	60.8
0°-40°	1432.0	84.2
0°-60°	1684.8	99.0
0°-90°	1701.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1701.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1545	
5°	1535	146
15°	1441	400
25°	1073	489
35°	639	397
45°	252	198
55°	56	55
65°	12	13
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P789293

CATALOG NUMBER: LER6D10D010-EC6DR650210IC9027-6LBS1LI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1544.9
2.5°	1543.7
5°	1535.1
7.5°	1530.1
10°	1516.3
12.5°	1488.1
15°	1441.3
17.5°	1368.2
20°	1276.5
22.5°	1177.5
25°	1072.9
27.5°	961.0
30°	852.7
32.5°	745.8
35°	639.1
37.5°	532.6
40°	431.3
42.5°	336.4
45°	251.5
47.5°	175.3
50°	119.2
52.5°	82.2
55°	56.5
57.5°	38.1
60°	25.9
62.5°	17.9
65°	12.0
67.5°	6.1
70°	4.1
72.5°	3.9
75°	3.4
77.5°	2.3
80°	1.6
82.5°	1.1
85°	0.7
87.5°	0.5
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)