

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P789311

Luminaire Tested: LER6D10D010-EC6DR650210IC9040-6LBDP1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P789311
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D10D010-EC6DR650210IC9040-6LBDP1B
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1284.5 lumens
Efficiency: N/A
Efficacy: 109.8 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P789311

CATALOG NUMBER: LER6D10D010-EC6DR650210IC9040-6LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P789311

CATALOG NUMBER: LER6D10D010-EC6DR650210IC9040-6LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87																			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80																			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69																			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65																			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60																			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57																			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53																			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	138182
5°	138293
10°	143165
15°	143396
20°	132028
25°	112491
30°	86119
35°	60836
40°	35914
45°	14587
50°	5286
55°	2953
60°	1683
65°	931
70°	990
75°	760
80°	818
85°	627

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 14587 cd/sqm



TEST NUMBER: P789311

CATALOG NUMBER: LER6D10D010-EC6DR650210IC9040-6LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	121.8	9.5
10°-20°	351.3	27.3
20°-30°	421.5	32.8
30°-40°	283.2	22.0
40°-50°	84.8	6.6
50°-60°	15.0	1.2
60°-70°	4.2	0.3
70°-80°	2.1	0.2
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	894.5	69.6
0°-40°	1177.8	91.7
0°-60°	1277.5	99.5
0°-90°	1284.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1284.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1265	
5°	1261	122
15°	1268	351
25°	933	421
35°	456	283
45°	94	85
55°	16	15
65°	4	4
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P789311

CATALOG NUMBER: LER6D10D010-EC6DR650210IC9040-6LBDP1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	1264.7
2.5°	1270.1
5°	1260.9
7.5°	1280.0
10°	1290.4
12.5°	1287.9
15°	1267.7
17.5°	1218.5
20°	1135.5
22.5°	1037.7
25°	933.1
27.5°	815.0
30°	682.6
32.5°	562.5
35°	456.1
37.5°	351.0
40°	251.8
42.5°	164.4
45°	94.4
47.5°	50.0
50°	31.1
52.5°	21.6
55°	15.5
57.5°	11.1
60°	7.7
62.5°	5.0
65°	3.6
67.5°	3.2
70°	3.1
72.5°	2.3
75°	1.8
77.5°	1.6
80°	1.3
82.5°	0.9
85°	0.5
87.5°	0.4
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)