

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P790592

Luminaire Tested: LER6D20D010-EC6DR7020359040-6LBDP1H

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P790592  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D20D010-EC6DR7020359040-6LBDP1H  
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3665.3 lumens  
Efficiency: N/A  
Efficacy: 158.7 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 23.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P790592

CATALOG NUMBER: LER6D20D010-EC6DR7020359040-6LBDP1H

### Luminous Intensity Polar Plot





TEST NUMBER: P790592

CATALOG NUMBER: LER6D20D010-EC6DR7020359040-6LBDP1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	450253
5°	436870
10°	424691
15°	419125
20°	391374
25°	294024
30°	207842
35°	73627
40°	38710
45°	41241
50°	42699
55°	43508
60°	43770
65°	42839
70°	40443
75°	37445
80°	33222
85°	26953

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 57.5°  
 Luminance: 43782 cd/sqm



TEST NUMBER: P790592

CATALOG NUMBER: LER6D20D010-EC6DR7020359040-6LBDP1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	375.7	10.3
10°-20°	1030.5	28.1
20°-30°	1135.0	31.0
30°-40°	433.6	11.8
40°-50°	204.8	5.6
50°-60°	203.6	5.6
60°-70°	163.0	4.4
70°-80°	93.7	2.6
80°-90°	25.5	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2541.2	69.3
0°-40°	2974.9	81.2
0°-60°	3383.2	92.3
0°-90°	3665.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3665.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4121	
5°	3983	376
15°	3705	1031
25°	2439	1135
35°	552	434
45°	267	205
55°	228	204
65°	166	163
75°	89	94
85°	22	25
90°	0	



TEST NUMBER: P790592

CATALOG NUMBER: LER6D20D010-EC6DR7020359040-6LBDP1H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4120.9
2.5°	4077.8
5°	3983.2
7.5°	3904.3
10°	3827.9
12.5°	3763.3
15°	3705.3
17.5°	3565.0
20°	3366.0
22.5°	2936.7
25°	2438.9
27.5°	2123.1
30°	1647.4
32.5°	1064.1
35°	552.0
37.5°	298.2
40°	271.4
42.5°	269.5
45°	266.9
47.5°	261.0
50°	251.2
52.5°	240.1
55°	228.4
57.5°	215.3
60°	200.3
62.5°	183.3
65°	165.7
67.5°	146.1
70°	126.6
72.5°	107.0
75°	88.7
77.5°	69.8
80°	52.8
82.5°	37.2
85°	21.5
87.5°	8.5
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)