

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P790601

Luminaire Tested: LER6D20D010-EC6DR7020359050-6LBDP1LI

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P790601  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D20D010-EC6DR7020359050-6LBDP1LI  
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3803.1 lumens  
Efficiency: N/A  
Efficacy: 164.6 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 23.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P790601  
CATALOG NUMBER: LER6D20D010-EC6DR7020359050-6LBDP1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P790601

CATALOG NUMBER: LER6D20D010-EC6DR7020359050-6LBDP1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	467188
5°	453300
10°	440668
15°	434882
20°	406095
25°	305079
30°	215664
35°	76388
40°	40165
45°	42786
50°	44297
55°	45127
60°	45409
65°	44468
70°	41945
75°	38880
80°	34481
85°	27956

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 57.5°  
 Luminance: 45429 cd/sqm



TEST NUMBER: P790601

CATALOG NUMBER: LER6D20D010-EC6DR7020359050-6LBDP1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	389.8	10.3
10°-20°	1069.3	28.1
20°-30°	1177.7	31.0
30°-40°	450.0	11.8
40°-50°	212.5	5.6
50°-60°	211.2	5.6
60°-70°	169.1	4.4
70°-80°	97.2	2.6
80°-90°	26.4	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2636.8	69.3
0°-40°	3086.8	81.2
0°-60°	3510.4	92.3
0°-90°	3803.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3803.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4276	
5°	4133	390
15°	3845	1069
25°	2531	1178
35°	573	450
45°	277	212
55°	237	211
65°	172	169
75°	92	97
85°	22	26
90°	0	



TEST NUMBER: P790601

CATALOG NUMBER: LER6D20D010-EC6DR7020359050-6LBDP1LI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	4275.9
2.5°	4231.2
5°	4133.0
7.5°	4051.1
10°	3971.9
12.5°	3904.9
15°	3844.6
17.5°	3699.1
20°	3492.6
22.5°	3047.1
25°	2530.6
27.5°	2202.9
30°	1709.4
32.5°	1104.2
35°	572.7
37.5°	309.4
40°	281.6
42.5°	279.6
45°	276.9
47.5°	270.8
50°	260.6
52.5°	249.1
55°	236.9
57.5°	223.4
60°	207.8
62.5°	190.2
65°	172.0
67.5°	151.6
70°	131.3
72.5°	111.0
75°	92.1
77.5°	72.4
80°	54.8
82.5°	38.6
85°	22.3
87.5°	8.8
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)