

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P789323

Luminaire Tested: LER6D10D010-EC6DR650210IC9050-6LBS1B

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P789323  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D10D010-EC6DR650210IC9050-6LBS1B  
Description: 6 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1665.4 lumens  
Efficiency: N/A  
Efficacy: 142.3 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96  
Luminous Opening: Circular (Dia: 0.48' x H: 0')  
CIE Type: Direct


Input Watts (W): 11.7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P789323  
CATALOG NUMBER: LER6D10D010-EC6DR650210IC9050-6LBS1B

### Luminous Intensity Polar Plot





TEST NUMBER: P789323

CATALOG NUMBER: LER6D10D010-EC6DR650210IC9050-6LBS1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93			93																
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85			85																
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78			78																
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72			72																
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66			66																
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61			61																
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56			56																
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			52																
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49			49																
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46			46																

**AVERAGE LUMINANCE (cd/sqm):**

0°	
0°	88318
5°	88093
10°	88020
15°	85303
20°	77659
25°	67677
30°	56285
35°	44597
40°	32189
45°	20335
50°	10603
55°	5631
60°	2955
65°	1631
70°	683
75°	745
80°	538
85°	469

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 20335 cd/sqm



TEST NUMBER: P789323

CATALOG NUMBER: LER6D10D010-EC6DR650210IC9050-6LBS1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	143.0	8.6
10°-20°	391.6	23.5
20°-30°	478.7	28.7
30°-40°	388.4	23.3
40°-50°	193.5	11.6
50°-60°	54.0	3.2
60°-70°	12.3	0.7
70°-80°	3.2	0.2
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1013.3	60.8
0°-40°	1401.6	84.2
0°-60°	1649.1	99.0
0°-90°	1665.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1665.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1512	
5°	1503	143
15°	1411	392
25°	1050	479
35°	626	388
45°	246	194
55°	55	54
65°	12	12
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P789323

CATALOG NUMBER: LER6D10D010-EC6DR650210IC9050-6LBS1B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1512.2
2.5°	1511.1
5°	1502.6
7.5°	1497.7
10°	1484.2
12.5°	1456.6
15°	1410.8
17.5°	1339.3
20°	1249.5
22.5°	1152.6
25°	1050.2
27.5°	940.6
30°	834.6
32.5°	730.0
35°	625.5
37.5°	521.3
40°	422.2
42.5°	329.3
45°	246.2
47.5°	171.6
50°	116.7
52.5°	80.4
55°	55.3
57.5°	37.3
60°	25.3
62.5°	17.6
65°	11.8
67.5°	6.0
70°	4.0
72.5°	3.8
75°	3.3
77.5°	2.2
80°	1.6
82.5°	1.1
85°	0.7
87.5°	0.4
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)