

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P789368

Luminaire Tested: LER6D10D010-EC6DR700210IC9050-6LBDP1H

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P789368  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D10D010-EC6DR700210IC9050-6LBDP1H  
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1963.0 lumens  
Efficiency: N/A  
Efficacy: 167.8 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 11.7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P789368  
CATALOG NUMBER: LER6D10D010-EC6DR700210IC9050-6LBDP1H

### Luminous Intensity Polar Plot





TEST NUMBER: P789368

CATALOG NUMBER: LER6D10D010-EC6DR700210IC9050-6LBDP1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	241138
5°	233976
10°	227451
15°	224466
20°	209605
25°	157470
30°	111314
35°	39428
40°	20738
45°	22081
50°	22862
55°	23297
60°	23447
65°	22958
70°	21659
75°	20052
80°	17807
85°	14417

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 60°  
 Luminance: 23447 cd/sqm



TEST NUMBER: P789368

CATALOG NUMBER: LER6D10D010-EC6DR700210IC9050-6LBDP1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	201.2	10.3
10°-20°	551.9	28.1
20°-30°	607.9	31.0
30°-40°	232.2	11.8
40°-50°	109.7	5.6
50°-60°	109.0	5.6
60°-70°	87.3	4.4
70°-80°	50.2	2.6
80°-90°	13.6	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1361.0	69.3
0°-40°	1593.3	81.2
0°-60°	1811.9	92.3
0°-90°	1963.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1963.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2207	
5°	2133	201
15°	1984	552
25°	1306	608
35°	296	232
45°	143	110
55°	122	109
65°	89	87
75°	48	50
85°	12	14
90°	0	



TEST NUMBER: P789368

CATALOG NUMBER: LER6D10D010-EC6DR700210IC9050-6LBDP1H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2207.0
2.5°	2184.0
5°	2133.3
7.5°	2091.0
10°	2050.1
12.5°	2015.5
15°	1984.4
17.5°	1909.3
20°	1802.7
22.5°	1572.8
25°	1306.2
27.5°	1137.1
30°	882.3
32.5°	569.9
35°	295.6
37.5°	159.7
40°	145.4
42.5°	144.3
45°	142.9
47.5°	139.8
50°	134.5
52.5°	128.6
55°	122.3
57.5°	115.3
60°	107.3
62.5°	98.2
65°	88.8
67.5°	78.3
70°	67.8
72.5°	57.3
75°	47.5
77.5°	37.4
80°	28.3
82.5°	19.9
85°	11.5
87.5°	4.5
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)