

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P789369

Luminaire Tested: LER6D10D010-EC6DR700210IC9050-6LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P789369
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D10D010-EC6DR700210IC9050-6LBDP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2061.2 lumens
Efficiency: N/A
Efficacy: 176.2 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P789369
CATALOG NUMBER: LER6D10D010-EC6DR700210IC9050-6LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P789369

CATALOG NUMBER: LER6D10D010-EC6DR700210IC9050-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	253201
5°	245679
10°	238823
15°	235698
20°	220093
25°	165342
30°	116878
35°	41402
40°	21765
45°	23193
50°	24018
55°	24459
60°	24606
65°	24095
70°	22745
75°	21065
80°	18687
85°	15169

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 24626 cd/sqm



TEST NUMBER: P789369

CATALOG NUMBER: LER6D10D010-EC6DR700210IC9050-6LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	211.3	10.3
10°-20°	579.5	28.1
20°-30°	638.3	31.0
30°-40°	243.9	11.8
40°-50°	115.2	5.6
50°-60°	114.5	5.6
60°-70°	91.7	4.4
70°-80°	52.7	2.6
80°-90°	14.3	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1429.1	69.3
0°-40°	1672.9	81.2
0°-60°	1902.5	92.3
0°-90°	2061.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2061.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2317	
5°	2240	211
15°	2084	580
25°	1372	638
35°	310	244
45°	150	115
55°	128	114
65°	93	92
75°	50	53
85°	12	14
90°	0	



TEST NUMBER: P789369

CATALOG NUMBER: LER6D10D010-EC6DR700210IC9050-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	2317.4
2.5°	2293.2
5°	2240.0
7.5°	2195.6
10°	2152.6
12.5°	2116.3
15°	2083.7
17.5°	2004.8
20°	1892.9
22.5°	1651.4
25°	1371.5
27.5°	1193.9
30°	926.4
32.5°	598.4
35°	310.4
37.5°	167.7
40°	152.6
42.5°	151.5
45°	150.1
47.5°	146.8
50°	141.3
52.5°	135.0
55°	128.4
57.5°	121.1
60°	112.6
62.5°	103.1
65°	93.2
67.5°	82.2
70°	71.2
72.5°	60.2
75°	49.9
77.5°	39.3
80°	29.7
82.5°	20.9
85°	12.1
87.5°	4.8
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)