

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P790682

Luminaire Tested: LER6D25D010-EC6DR2015309035-6LBDP1MW

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P790682  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D25D010-EC6DR2015309035-6LB DP1MW  
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 20° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2923.4 lumens  
Efficiency: N/A  
Efficacy: 116.5 lumens/watt  
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 25.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P790682  
CATALOG NUMBER: LER6D25D010-EC6DR2015309035-6LBDP1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P790682

CATALOG NUMBER: LER6D25D010-EC6DR2015309035-6LBDP1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	97	98	98	97															
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94	94	98	96	95															
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91	91	98	93	92															
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88	88	93	91	89															
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85	85	91	88	86															
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83	83	88	86	84															
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81	81	86	84	82															
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79	79	84	82	80															
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77	77	82	80	78															
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	75	75	81	78	76															

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1818022
5°	1640192
10°	920566
15°	467946
20°	198117
25°	91454
30°	48422
35°	26090
40°	13949
45°	8236
50°	4793
55°	2534
60°	1617
65°	1138
70°	479
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 8236 cd/sqm



TEST NUMBER: P790682

CATALOG NUMBER: LER6D25D010-EC6DR2015309035-6LBDP1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1184.7	40.5
10°-20°	1166.5	39.9
20°-30°	381.1	13.0
30°-40°	129.8	4.4
40°-50°	43.6	1.5
50°-60°	13.1	0.4
60°-70°	4.4	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2732.3	93.5
0°-40°	2862.1	97.9
0°-60°	2918.9	99.8
0°-90°	2923.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2923.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	16639	
5°	14955	###
15°	4137	1167
25°	759	381
35°	196	130
45°	53	44
55°	13	13
65°	4	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P790682

CATALOG NUMBER: LER6D25D010-EC6DR2015309035-6LBDP1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	16639.3
0.5°	16639.3
1°	16618.6
1.5°	16577.1
2°	16501.5
2.5°	16400.8
3°	16258.5
3.5°	16060.0
4°	15765.1
4.5°	15406.6
5°	14954.6
5.5°	14360.5
6°	13751.5
6.5°	13053.6
7°	12370.6
7.5°	11570.5
8°	10856.3
8.5°	10137.7
9°	9473.9
9.5°	8864.9
10°	8297.4
12.5°	5957.9
15°	4136.9
17.5°	2702.6
20°	1703.9
22.5°	1103.9
25°	758.6
27.5°	533.4
30°	383.8
32.5°	275.6
35°	195.6
37.5°	136.3
40°	97.8
42.5°	71.1
45°	53.3
47.5°	41.5
50°	28.2
52.5°	17.8
55°	13.3
57.5°	10.4
60°	7.4
62.5°	5.9
65°	4.4



TEST NUMBER: P790682

CATALOG NUMBER: LER6D25D010-EC6DR2015309035-6LBDP1MW

**CANDELA DISTRIBUTION (continued):**

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





67.5°		3.0
70°		1.5

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)