

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P789376

Luminaire Tested: LER6D15D010-EC6DR1015209024-6LBDP1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P789376
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D15D010-EC6DR1015209024-6LBDP1H
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 10° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1206.2 lumens
Efficiency: N/A
Efficacy: 76.3 lumens/watt
Spacing Criteria (0/90/45): 0.17 / 0.17 / 0.18
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P789376
CATALOG NUMBER: LER6D15D010-EC6DR1015209024-6LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P789376

CATALOG NUMBER: LER6D15D010-EC6DR1015209024-6LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	116	114	113	111	114	112	111	109	108	107	106	104	104	103	101	101	100	98			98																
2	113	110	108	106	111	108	106	104	105	104	102	103	101	100	100	99	98	97			97																
3	111	107	104	102	109	106	103	101	103	101	99	101	99	98	99	98	96	95			95																
4	108	104	101	99	107	103	100	98	101	99	97	99	97	96	98	96	95	94			94																
5	106	102	99	96	105	101	98	96	99	97	95	98	96	94	97	95	94	93			93																
6	104	100	96	94	103	99	96	94	98	95	93	97	94	93	96	94	92	91			91																
7	103	98	95	93	102	97	94	92	96	94	92	95	93	92	95	93	91	90			90																
8	101	96	93	91	100	96	93	91	95	92	91	94	92	90	93	92	90	89			89																
9	100	95	92	90	99	94	92	90	94	91	90	93	91	89	93	91	89	88			88																
10	98	94	91	89	98	93	91	89	93	90	88	92	90	88	92	90	88	87			87																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2869384
5°	1360656
10°	279052
15°	76613
20°	30870
25°	16540
30°	9790
35°	6362
40°	4250
45°	2766
50°	1530
55°	1143
60°	656
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2766 cd/sqm



TEST NUMBER: P789376

CATALOG NUMBER: LER6D15D010-EC6DR1015209024-6LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	857.6	71.1
10°-20°	232.1	19.2
20°-30°	66.4	5.5
30°-40°	30.3	2.5
40°-50°	13.9	1.2
50°-60°	4.7	0.4
60°-70°	1.1	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1156.2	95.9
0°-40°	1186.5	98.4
0°-60°	1205.1	99.9
0°-90°	1206.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1206.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	26262	
5°	12406	858
15°	677	232
25°	137	66
35°	48	30
45°	18	14
55°	6	5
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P789376

CATALOG NUMBER: LER6D15D010-EC6DR1015209024-6LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	26261.8
0.5°	26035.1
1°	25453.3
1.5°	24331.4
2°	23075.3
2.5°	21416.4
3°	19572.5
3.5°	17788.3
4°	15863.9
4.5°	14091.6
5°	12405.9
5.5°	10878.3
6°	9422.3
6.5°	8142.3
7°	6936.9
7.5°	5907.6
8°	4994.6
8.5°	4195.0
9°	3502.8
9.5°	2974.7
10°	2515.2
12.5°	1199.4
15°	677.3
17.5°	411.7
20°	265.5
22.5°	185.0
25°	137.2
27.5°	101.4
30°	77.6
32.5°	59.7
35°	47.7
37.5°	35.8
40°	29.8
42.5°	23.9
45°	17.9
47.5°	11.9
50°	9.0
52.5°	6.0
55°	6.0
57.5°	3.0
60°	3.0
62.5°	3.0
65°	0.0



TEST NUMBER: P789376

CATALOG NUMBER: LER6D15D010-EC6DR1015209024-6LBDP1H

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



67.5°		0.0
70°		0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)