

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P790702

Luminaire Tested: LER6D25D010-EC6DR2015309050-6LBS1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P790702
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D25D010-EC6DR2015309050-6LBS1MW
Description: 6 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 20° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3221.3 lumens
Efficiency: N/A
Efficacy: 128.3 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 25.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P790702

CATALOG NUMBER: LER6D25D010-EC6DR2015309050-6LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P790702

CATALOG NUMBER: LER6D25D010-EC6DR2015309050-6LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	97	98	98	97															
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94	94	98	96	95															
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91	91	98	96	95															
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88	88	96	94	93															
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85	85	94	92	91															
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83	83	92	90	89															
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81	81	90	88	87															
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79	79	88	86	85															
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77	77	86	84	83															
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	75	75	84	82	81															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2003285
5°	1807331
10°	1014382
15°	515624
20°	218314
25°	100773
30°	53355
35°	28744
40°	15375
45°	9086
50°	5269
55°	2800
60°	1792
65°	1267
70°	511
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 9086 cd/sqm



TEST NUMBER: P790702

CATALOG NUMBER: LER6D25D010-EC6DR2015309050-6LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1305.4	40.5
10°-20°	1285.4	39.9
20°-30°	419.9	13.0
30°-40°	143.0	4.4
40°-50°	48.1	1.5
50°-60°	14.5	0.4
60°-70°	4.8	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3010.8	93.5
0°-40°	3153.7	97.9
0°-60°	3216.3	99.8
0°-90°	3221.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3221.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	18335	
5°	16478	###
15°	4558	1285
25°	836	420
35°	216	143
45°	59	48
55°	15	14
65°	5	5
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P790702

CATALOG NUMBER: LER6D25D010-EC6DR2015309050-6LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	18334.9
0.5°	18334.9
1°	18312.0
1.5°	18266.3
2°	18183.0
2.5°	18072.0
3°	17915.3
3.5°	17696.5
4°	17371.6
4.5°	16976.5
5°	16478.5
5.5°	15823.8
6°	15152.8
6.5°	14383.8
7°	13631.2
7.5°	12749.5
8°	11962.6
8.5°	11170.7
9°	10439.3
9.5°	9768.3
10°	9143.0
12.5°	6565.0
15°	4558.4
17.5°	2978.0
20°	1877.6
22.5°	1216.3
25°	835.9
27.5°	587.8
30°	422.9
32.5°	303.7
35°	215.5
37.5°	150.2
40°	107.8
42.5°	78.4
45°	58.8
47.5°	45.7
50°	31.0
52.5°	19.6
55°	14.7
57.5°	11.4
60°	8.2
62.5°	6.5
65°	4.9



TEST NUMBER: P790702

CATALOG NUMBER: LER6D25D010-EC6DR2015309050-6LBS1MW

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





67.5°		3.3
70°		1.6

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)