

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P791023

Luminaire Tested: LER6D25D010-EC6DR5520359040-6LBDP1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P791023
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-52)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D25D010-EC6DR5520359040-6LBDDP1B
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 55° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4328.9 lumens
Efficiency: N/A
Efficacy: 172.5 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.87
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 25.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P791023
CATALOG NUMBER: LER6D25D010-EC6DR5520359040-6LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P791023

CATALOG NUMBER: LER6D25D010-EC6DR5520359040-6LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94			94																
2	108	103	99	96	106	101	98	95	98	95	92	95	93	90	92	90	89	87			87																
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			81																
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75			75																
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70			70																
6	88	79	73	68	86	78	72	68	76	71	68	75	70	67	74	70	67	65			65																
7	83	74	68	64	82	73	67	63	72	67	63	71	66	63	70	65	62	61			61																
8	79	69	63	59	78	69	63	59	68	63	59	67	62	59	66	62	58	57			57																
9	75	66	60	56	74	65	59	55	64	59	55	63	58	55	62	58	55	54			54																
10	72	62	56	52	71	61	56	52	61	56	52	60	55	52	59	55	52	50			50																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	530363
5°	509301
10°	507380
15°	492808
20°	441872
25°	365188
30°	275856
35°	200021
40°	127996
45°	58454
50°	19123
55°	8248
60°	3540
65°	465
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 58454 cd/sqm



TEST NUMBER: P791023

CATALOG NUMBER: LER6D25D010-EC6DR5520359040-6LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	441.9	10.2
10°-20°	1205.9	27.9
20°-30°	1374.3	31.7
30°-40°	935.6	21.6
40°-50°	322.4	7.4
50°-60°	44.6	1.0
60°-70°	4.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3022.1	69.8
0°-40°	3957.6	91.4
0°-60°	4324.6	99.9
0°-90°	4328.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4328.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4854	
5°	4644	442
15°	4357	1206
25°	3029	1374
35°	1500	936
45°	378	322
55°	43	45
65°	2	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P791023

CATALOG NUMBER: LER6D25D010-EC6DR5520359040-6LBDP1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	4854.1
2.5°	4742.9
5°	4643.6
7.5°	4594.9
10°	4573.2
12.5°	4501.1
15°	4356.7
17.5°	4127.5
20°	3800.3
22.5°	3422.6
25°	3029.2
27.5°	2619.6
30°	2186.5
32.5°	1819.6
35°	1499.6
37.5°	1195.2
40°	897.4
42.5°	622.0
45°	378.3
47.5°	203.9
50°	112.5
52.5°	66.8
55°	43.3
57.5°	27.7
60°	16.2
62.5°	7.2
65°	1.8
67.5°	0.6
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)