

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P789571

Luminaire Tested: LER6D15D010-EC6DR300215IC9027-6LBDP1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P789571
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D15D010-EC6DR300215IC9027-6LBDP1B
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1856.0 lumens
Efficiency: N/A
Efficacy: 117.5 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct


Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P789571
CATALOG NUMBER: LER6D15D010-EC6DR300215IC9027-6LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P789571

CATALOG NUMBER: LER6D15D010-EC6DR300215IC9027-6LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																			
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89																			
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85																			
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82																			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																			
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																			
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72																			
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	456796	456796	456796
5°	443681	443158	443704
10°	384292	381587	384206
15°	250735	249387	248135
20°	124676	129352	124513
25°	62802	70825	61518
30°	25145	27399	21911
35°	11662	11166	9363
40°	5036	5596	4746
45°	3551	4406	3583
50°	1227	3215	1286
55°	707	1334	747
60°	490	582	490
65°	326	326	326
70°	201	134	201
75°	0	89	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 4406 cd/sqm



TEST NUMBER: P789571

CATALOG NUMBER: LER6D15D010-EC6DR300215IC9027-6LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	524.8	28.3
10°-20°	845.2	45.5
20°-30°	365.2	19.7
30°-40°	83.2	4.5
40°-50°	28.6	1.5
50°-60°	7.0	0.4
60°-70°	1.8	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1735.1	93.5
0°-40°	1818.4	98.0
0°-60°	1854.0	99.9
0°-90°	1856.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1856.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	5968	5968	5968	5968	5968	
5°	5774	5769	5768	5780	5775	525
15°	3164	3126	3147	3137	3131	847
25°	744	772	839	752	728	356
35°	125	128	120	119	100	85
45°	33	41	41	41	33	23
55°	5	6	10	6	6	5
65°	2	2	2	2	2	2
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P789571

CATALOG NUMBER: LER6D15D010-EC6DR300215IC9027-6LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	5967.8	5967.8	5967.8	5967.8	5967.8
2.5°	5928.2	5924.1	5926.5	5929.4	5930.6
5°	5774.4	5768.8	5767.6	5779.7	5774.7
7.5°	5464.1	5456.2	5444.2	5471.4	5496.9
10°	4944.3	4935.5	4909.5	4922.4	4943.2
12.5°	4177.0	4148.5	4148.0	4189.0	4183.4
15°	3164.1	3126.0	3147.1	3136.8	3131.3
17.5°	2127.7	2113.1	2141.2	2132.7	2096.1
20°	1530.6	1534.4	1588.0	1561.1	1528.6
22.5°	1116.9	1130.7	1194.3	1124.8	1099.3
25°	743.6	771.8	838.6	752.1	728.4
27.5°	457.4	470.3	537.9	451.5	438.6
30°	284.5	278.1	310.0	266.0	247.9
32.5°	186.6	178.4	188.7	169.4	154.7
35°	124.8	127.5	119.5	118.7	100.2
37.5°	77.9	89.7	79.1	84.4	64.5
40°	50.4	65.0	56.0	61.8	47.5
42.5°	41.3	50.1	46.0	48.9	42.2
45°	32.8	40.7	40.7	40.7	33.1
47.5°	18.2	27.2	34.9	27.8	19.3
50°	10.3	13.8	27.0	14.4	10.8
52.5°	7.0	7.9	18.5	8.2	7.3
55°	5.3	5.6	10.0	5.9	5.6
57.5°	4.1	4.4	5.3	4.4	4.1
60°	3.2	3.2	3.8	3.5	3.2
62.5°	2.3	2.3	2.6	2.3	2.3
65°	1.8	1.8	1.8	1.8	1.8
67.5°	0.9	1.2	1.2	1.2	1.2
70°	0.9	0.6	0.6	0.6	0.9
72.5°	0.6	0.3	0.3	0.3	0.3
75°	0.0	0.0	0.3	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)