

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P789574

Luminaire Tested: LER6D15D010-EC6DR300215IC9027-6LBDP1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P789574
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D15D010-EC6DR300215IC9027-6LBDP1MW
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2056.4 lumens
Efficiency: N/A
Efficacy: 130.2 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P789574

CATALOG NUMBER: LER6D15D010-EC6DR300215IC9027-6LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P789574

CATALOG NUMBER: LER6D15D010-EC6DR300215IC9027-6LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96								
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92								
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89								
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85								
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82								
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79								
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77								
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74								
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72								
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69								

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	506136	506136	506136
5°	491603	491027	491626
10°	425804	422804	425703
15°	277812	276322	274936
20°	138141	143330	137962
25°	69592	78468	68165
30°	27859	30360	24279
35°	12923	12381	10372
40°	5576	6195	5256
45°	3940	4882	3973
50°	1358	3561	1429
55°	774	1468	827
60°	551	643	551
65°	344	344	344
70°	224	134	224
75°	0	89	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 4882 cd/sqm



TEST NUMBER: P789574

CATALOG NUMBER: LER6D15D010-EC6DR300215IC9027-6LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	581.5	28.3
10°-20°	936.4	45.5
20°-30°	404.7	19.7
30°-40°	92.2	4.5
40°-50°	31.7	1.5
50°-60°	7.7	0.4
60°-70°	2.0	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1922.6	93.5
0°-40°	2014.8	98.0
0°-60°	2054.2	99.9
0°-90°	2056.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2056.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	6612	6612	6612	6612	6612	
5°	6398	6392	6391	6404	6398	582
15°	3506	3464	3487	3476	3470	939
25°	824	855	929	833	807	394
35°	138	141	132	132	111	94
45°	36	45	45	45	37	26
55°	6	6	11	6	6	6
65°	2	2	2	2	2	2
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P789574

CATALOG NUMBER: LER6D15D010-EC6DR300215IC9027-6LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	6612.4	6612.4	6612.4	6612.4	6612.4
2.5°	6568.6	6564.0	6566.6	6569.9	6571.2
5°	6398.1	6391.9	6390.6	6404.0	6398.4
7.5°	6054.3	6045.6	6032.2	6062.4	6090.7
10°	5478.4	5468.7	5439.8	5454.0	5477.1
12.5°	4628.1	4596.7	4596.0	4641.5	4635.3
15°	3505.8	3463.6	3487.0	3475.7	3469.5
17.5°	2357.6	2341.3	2372.5	2363.1	2322.5
20°	1695.9	1700.2	1759.6	1729.7	1693.7
22.5°	1237.5	1252.8	1323.3	1246.3	1218.1
25°	824.0	855.1	929.1	833.4	807.1
27.5°	506.8	521.1	596.0	500.3	486.0
30°	315.2	308.1	343.5	294.8	274.7
32.5°	206.8	197.7	209.1	187.6	171.4
35°	138.3	141.2	132.5	131.5	111.0
37.5°	86.4	99.3	87.7	93.5	71.4
40°	55.8	72.1	62.0	68.5	52.6
42.5°	45.8	55.5	51.0	54.2	46.7
45°	36.4	45.1	45.1	45.1	36.7
47.5°	20.1	30.2	38.6	30.8	21.4
50°	11.4	15.3	29.9	15.9	12.0
52.5°	7.8	8.8	20.5	9.1	8.1
55°	5.8	6.2	11.0	6.5	6.2
57.5°	4.5	4.9	5.8	4.9	4.5
60°	3.6	3.6	4.2	3.9	3.6
62.5°	2.6	2.6	2.9	2.6	2.6
65°	1.9	1.9	1.9	1.9	1.9
67.5°	1.0	1.3	1.3	1.3	1.3
70°	1.0	0.6	0.6	0.6	1.0
72.5°	0.6	0.3	0.3	0.3	0.3
75°	0.0	0.0	0.3	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)