

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P789605

Luminaire Tested: LER6D15D010-EC6DR300215IC9050-6LBDP1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P789605
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D15D010-EC6DR300215IC9050-6LBDP1MW
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2276.4 lumens
Efficiency: N/A
Efficacy: 144.1 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P789605

CATALOG NUMBER: LER6D15D010-EC6DR300215IC9050-6LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P789605

CATALOG NUMBER: LER6D15D010-EC6DR300215IC9050-6LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96						96													
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92						92													
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89						89													
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85						85													
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82						82													
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79						79													
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77						77													
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74						74													
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72						72													
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69						69													

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	560282	560282	560282
5°	544197	543559	544220
10°	471358	468032	471242
15°	307536	305880	304343
20°	152925	158660	152721
25°	77033	86863	75453
30°	30846	33604	26869
35°	14306	13699	11484
40°	6175	6855	5815
45°	4362	5412	4395
50°	1500	3942	1584
55°	867	1628	907
60°	612	720	612
65°	398	398	398
70°	246	157	246
75°	0	118	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 5412 cd/sqm



TEST NUMBER: P789605

CATALOG NUMBER: LER6D15D010-EC6DR300215IC9050-6LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	643.7	28.3
10°-20°	1036.6	45.5
20°-30°	447.9	19.7
30°-40°	102.1	4.5
40°-50°	35.1	1.5
50°-60°	8.6	0.4
60°-70°	2.2	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2128.2	93.5
0°-40°	2230.3	98.0
0°-60°	2274.0	99.9
0°-90°	2276.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2276.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	7320	7320	7320	7320	7320	
5°	7083	7076	7074	7089	7083	644
15°	3881	3834	3860	3848	3841	1039
25°	912	947	1028	922	893	437
35°	153	156	147	146	123	104
45°	40	50	50	50	41	29
55°	6	7	12	7	7	6
65°	2	2	2	2	2	2
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P789605

CATALOG NUMBER: LER6D15D010-EC6DR300215IC9050-6LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	7319.8	7319.8	7319.8	7319.8	7319.8
2.5°	7271.2	7266.2	7269.1	7272.7	7274.1
5°	7082.6	7075.7	7074.3	7089.0	7082.9
7.5°	6702.0	6692.3	6677.5	6711.0	6742.2
10°	6064.5	6053.7	6021.7	6037.5	6063.0
12.5°	5123.3	5088.4	5087.7	5138.0	5131.2
15°	3880.9	3834.2	3860.0	3847.5	3840.6
17.5°	2609.8	2591.8	2626.3	2615.9	2571.0
20°	1877.4	1882.0	1947.8	1914.8	1874.9
22.5°	1369.9	1386.8	1464.8	1379.6	1348.4
25°	912.1	946.6	1028.5	922.5	893.4
27.5°	561.0	576.8	659.8	553.8	538.0
30°	349.0	341.0	380.2	326.3	304.0
32.5°	228.9	218.9	231.4	207.7	189.8
35°	153.1	156.3	146.6	145.5	122.9
37.5°	95.6	110.0	97.0	103.5	79.1
40°	61.8	79.8	68.6	75.8	58.2
42.5°	50.7	61.5	56.4	60.0	51.8
45°	40.3	50.0	50.0	50.0	40.6
47.5°	22.3	33.4	42.8	34.1	23.7
50°	12.6	16.9	33.1	17.6	13.3
52.5°	8.6	9.7	22.6	10.1	9.0
55°	6.5	6.8	12.2	7.2	6.8
57.5°	5.0	5.4	6.5	5.4	5.0
60°	4.0	4.0	4.7	4.3	4.0
62.5°	2.9	2.9	3.2	2.9	2.9
65°	2.2	2.2	2.2	2.2	2.2
67.5°	1.1	1.4	1.4	1.4	1.4
70°	1.1	0.7	0.7	0.7	1.1
72.5°	0.7	0.4	0.4	0.4	0.4
75°	0.0	0.0	0.4	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)