

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P791050

Luminaire Tested: LER6D25D010-EC6DR6020359027-6LBDP1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P791050
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D25D010-EC6DR6020359027-6LBDP1MW
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4352.9 lumens
Efficiency: N/A
Efficacy: 173.4 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 25.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P791050
CATALOG NUMBER: LER6D25D010-EC6DR6020359027-6LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P791050

CATALOG NUMBER: LER6D25D010-EC6DR6020359027-6LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93																
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86			86																
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80			80																
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75			75																
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			70																
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66			66																
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62			62																
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59			59																
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			55																
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53			53																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	564834
5°	578717
10°	585708
15°	557963
20°	491950
25°	397907
30°	269157
35°	134877
40°	21879
45°	21416
50°	21842
55°	22173
60°	22792
65°	23320
70°	23863
75°	24147
80°	23281
85°	19431

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 24147 cd/sqm



TEST NUMBER: P791050

CATALOG NUMBER: LER6D25D010-EC6DR6020359027-6LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	504.3	11.6
10°-20°	1364.4	31.3
20°-30°	1468.0	33.7
30°-40°	638.1	14.7
40°-50°	107.2	2.5
50°-60°	104.2	2.4
60°-70°	89.2	2.0
70°-80°	59.6	1.4
80°-90°	17.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3336.7	76.7
0°-40°	3974.8	91.3
0°-60°	4186.2	96.2
0°-90°	4352.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4352.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5170	
5°	5276	504
15°	4933	1364
25°	3301	1468
35°	1011	638
45°	139	107
55°	116	104
65°	90	89
75°	57	60
85°	16	18
90°	0	



TEST NUMBER: P791050

CATALOG NUMBER: LER6D25D010-EC6DR6020359027-6LBDP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	5169.6
2.5°	5314.9
5°	5276.5
7.5°	5288.6
10°	5279.2
12.5°	5170.2
15°	4932.7
17.5°	4613.9
20°	4231.0
22.5°	3821.3
25°	3300.6
27.5°	2639.9
30°	2133.4
32.5°	1644.2
35°	1011.2
37.5°	432.6
40°	153.4
42.5°	141.3
45°	138.6
47.5°	133.9
50°	128.5
52.5°	122.4
55°	116.4
57.5°	110.3
60°	104.3
62.5°	97.6
65°	90.2
67.5°	82.8
70°	74.7
72.5°	65.9
75°	57.2
77.5°	47.1
80°	37.0
82.5°	26.2
85°	15.5
87.5°	5.4
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)