

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P789663

Luminaire Tested: LER6D15D010-EC6DR400215IC9024-6LBS1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P789663
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D15D010-EC6DR400215IC9024-6LBS1LI
Description: 6 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 40° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2453.7 lumens
Efficiency: N/A
Efficacy: 155.3 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P789663
CATALOG NUMBER: LER6D15D010-EC6DR400215IC9024-6LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P789663

CATALOG NUMBER: LER6D15D010-EC6DR400215IC9024-6LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100														
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	97	96					96														
2	110	106	103	100	108	105	102	99	102	99	97	99	97	95	96	95	93	92					92														
3	106	101	97	94	104	100	96	93	97	94	92	95	93	90	93	91	89	88					88														
4	102	97	92	89	101	95	91	88	93	90	87	92	89	86	90	87	85	84					84														
5	99	92	88	84	97	91	87	84	90	86	83	88	85	83	87	84	82	81					81														
6	95	88	84	80	94	88	83	80	86	82	80	85	82	79	84	81	79	77					77														
7	92	85	80	77	91	84	80	77	83	79	76	82	79	76	81	78	76	74					74														
8	89	82	77	74	88	81	77	74	80	76	73	79	76	73	78	75	73	72					72														
9	86	79	74	71	85	78	74	71	77	73	71	77	73	70	76	72	70	69					69														
10	83	76	71	68	82	75	71	68	75	71	68	74	70	68	73	70	68	67					67														

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	624185
5°	621151
10°	587128
15°	499131
20°	340191
25°	141943
30°	44637
35°	20741
40°	11467
45°	5254
50°	2550
55°	1391
60°	721
65°	259
70°	96
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 5254 cd/sqm



TEST NUMBER: P789663

CATALOG NUMBER: LER6D15D010-EC6DR400215IC9024-6LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	528.8	21.6
10°-20°	1184.7	48.3
20°-30°	593.0	24.2
30°-40°	108.7	4.4
40°-50°	30.0	1.2
50°-60°	7.0	0.3
60°-70°	1.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2306.5	94.0
0°-40°	2415.2	98.4
0°-60°	2452.3	99.9
0°-90°	2453.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2453.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5713	
5°	5663	529
15°	4413	1185
25°	1177	593
35°	156	109
45°	34	30
55°	7	7
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P789663

CATALOG NUMBER: LER6D15D010-EC6DR400215IC9024-6LBS1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	5712.8
2.5°	5704.5
5°	5663.4
7.5°	5532.6
10°	5292.0
12.5°	4916.9
15°	4412.6
17.5°	3756.8
20°	2925.8
22.5°	1994.7
25°	1177.4
27.5°	622.4
30°	353.8
32.5°	228.6
35°	155.5
37.5°	111.1
40°	80.4
42.5°	55.1
45°	34.0
47.5°	21.7
50°	15.0
52.5°	10.7
55°	7.3
57.5°	4.7
60°	3.3
62.5°	2.0
65°	1.0
67.5°	0.7
70°	0.3
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)