

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P791065

Luminaire Tested: LER6D25D010-EC6DR6020359035-6LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P791065
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D25D010-EC6DR6020359035-6LBDP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5501.4 lumens
Efficiency: N/A
Efficacy: 219.2 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 25.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P791065
CATALOG NUMBER: LER6D25D010-EC6DR6020359035-6LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P791065

CATALOG NUMBER: LER6D25D010-EC6DR6020359035-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86	86	86	86
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80	80	80	80
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75	75	75	75
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70	70	70	70
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66	66	66	66
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62	62	62	62
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59	59	59	59
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55	55	55	55
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53	53	53	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	713855
5°	731410
10°	740245
15°	705182
20°	621758
25°	502899
30°	340162
35°	170463
40°	27656
45°	27072
50°	27605
55°	28021
60°	28801
65°	29447
70°	30157
75°	30522
80°	29447
85°	24571

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 30522 cd/sqm



TEST NUMBER: P791065

CATALOG NUMBER: LER6D25D010-EC6DR6020359035-6LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	637.4	11.6
10°-20°	1724.4	31.3
20°-30°	1855.3	33.7
30°-40°	806.5	14.7
40°-50°	135.5	2.5
50°-60°	131.7	2.4
60°-70°	112.6	2.0
70°-80°	75.4	1.4
80°-90°	22.6	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4217.1	76.7
0°-40°	5023.6	91.3
0°-60°	5290.8	96.2
0°-90°	5501.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5501.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6534	
5°	6669	637
15°	6234	1724
25°	4172	1855
35°	1278	806
45°	175	135
55°	147	132
65°	114	113
75°	72	75
85°	20	23
90°	0	



TEST NUMBER: P791065

CATALOG NUMBER: LER6D25D010-EC6DR6020359035-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	6533.5
2.5°	6717.2
5°	6668.7
7.5°	6684.0
10°	6672.1
12.5°	6534.4
15°	6234.2
17.5°	5831.2
20°	5347.4
22.5°	4829.6
25°	4171.5
27.5°	3336.5
30°	2696.2
32.5°	2078.1
35°	1278.0
37.5°	546.7
40°	193.9
42.5°	178.6
45°	175.2
47.5°	169.2
50°	162.4
52.5°	154.8
55°	147.1
57.5°	139.4
60°	131.8
62.5°	123.3
65°	113.9
67.5°	104.6
70°	94.4
72.5°	83.3
75°	72.3
77.5°	59.5
80°	46.8
82.5°	33.2
85°	19.6
87.5°	6.8
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)