

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P791081

Luminaire Tested: LER6D25D010-EC6DR6020359050-6LBDP1LI

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P791081  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D25D010-EC6DR6020359050-6LBDDP1LI  
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 60° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5586.7 lumens  
Efficiency: N/A  
Efficacy: 222.6 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 25.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P791081  
CATALOG NUMBER: LER6D25D010-EC6DR6020359050-6LBDP1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P791081

CATALOG NUMBER: LER6D25D010-EC6DR6020359050-6LBDP1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	724945
5°	742773
10°	751739
15°	716131
20°	631408
25°	510699
30°	345448
35°	173104
40°	28084
45°	27489
50°	28030
55°	28459
60°	29238
65°	29912
70°	30604
75°	30986
80°	29887
85°	24947

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 75°  
 Luminance: 30986 cd/sqm



TEST NUMBER: P791081

CATALOG NUMBER: LER6D25D010-EC6DR6020359050-6LBDP1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	647.3	11.6
10°-20°	1751.2	31.3
20°-30°	1884.1	33.7
30°-40°	819.0	14.7
40°-50°	137.5	2.5
50°-60°	133.8	2.4
60°-70°	114.4	2.0
70°-80°	76.5	1.4
80°-90°	22.9	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4282.6	76.7
0°-40°	5101.6	91.3
0°-60°	5372.9	96.2
0°-90°	5586.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5586.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6635	
5°	6772	647
15°	6331	1751
25°	4236	1884
35°	1298	819
45°	178	138
55°	149	134
65°	116	114
75°	73	77
85°	20	23
90°	0	



TEST NUMBER: P791081

CATALOG NUMBER: LER6D25D010-EC6DR6020359050-6LBDP1LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	6635.0
2.5°	6821.5
5°	6772.3
7.5°	6787.8
10°	6775.7
12.5°	6635.9
15°	6331.0
17.5°	5921.8
20°	5430.4
22.5°	4904.6
25°	4236.2
27.5°	3388.3
30°	2738.1
32.5°	2110.3
35°	1297.8
37.5°	555.2
40°	196.9
42.5°	181.3
45°	177.9
47.5°	171.8
50°	164.9
52.5°	157.2
55°	149.4
57.5°	141.6
60°	133.8
62.5°	125.2
65°	115.7
67.5°	106.2
70°	95.8
72.5°	84.6
75°	73.4
77.5°	60.4
80°	47.5
82.5°	33.7
85°	19.9
87.5°	6.9
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)