

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P791107

Luminaire Tested: LER6D25D010-EC6DR6520359030-6LBS1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P791107
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D25D010-EC6DR6520359030-6LBS1B
Description: 6 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4238.3 lumens
Efficiency: N/A
Efficacy: 168.9 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct


Input Watts (W): 25.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P791107
CATALOG NUMBER: LER6D25D010-EC6DR6520359030-6LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P791107

CATALOG NUMBER: LER6D25D010-EC6DR6520359030-6LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93																			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78																			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72																			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66																			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61																			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56																			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52																			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49																			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	224750
5°	224184
10°	223994
15°	217084
20°	197631
25°	172220
30°	143240
35°	113499
40°	81913
45°	51754
50°	26976
55°	14337
60°	7534
65°	4146
70°	1742
75°	1918
80°	1345
85°	1139

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 51754 cd/sqm



TEST NUMBER: P791107

CATALOG NUMBER: LER6D25D010-EC6DR6520359030-6LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	363.9	8.6
10°-20°	996.5	23.5
20°-30°	1218.1	28.7
30°-40°	988.4	23.3
40°-50°	492.5	11.6
50°-60°	137.4	3.2
60°-70°	31.2	0.7
70°-80°	8.1	0.2
80°-90°	2.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2578.6	60.8
0°-40°	3566.9	84.2
0°-60°	4196.8	99.0
0°-90°	4238.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4238.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3848	
5°	3824	364
15°	3590	997
25°	2672	1218
35°	1592	988
45°	627	493
55°	141	137
65°	30	31
75°	8	8
85°	2	2
90°	0	



TEST NUMBER: P791107

CATALOG NUMBER: LER6D25D010-EC6DR6520359030-6LBS1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	3848.2
2.5°	3845.4
5°	3823.9
7.5°	3811.4
10°	3777.0
12.5°	3706.8
15°	3590.3
17.5°	3408.2
20°	3179.8
22.5°	2933.2
25°	2672.5
27.5°	2393.7
30°	2124.0
32.5°	1857.7
35°	1591.9
37.5°	1326.7
40°	1074.4
42.5°	838.1
45°	626.6
47.5°	436.6
50°	296.9
52.5°	204.7
55°	140.8
57.5°	95.0
60°	64.5
62.5°	44.7
65°	30.0
67.5°	15.3
70°	10.2
72.5°	9.6
75°	8.5
77.5°	5.7
80°	4.0
82.5°	2.8
85°	1.7
87.5°	1.1
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)