

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P789869

Luminaire Tested: LER6D15D010-EC6DR600215IC9035-6LBDP1B

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P789869  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D15D010-EC6DR600215IC9035-6LBDP1B  
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 60° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2032.1 lumens  
Efficiency: N/A  
Efficacy: 128.6 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 15.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P789869  
CATALOG NUMBER: LER6D15D010-EC6DR600215IC9035-6LBDP1B

### Luminous Intensity Polar Plot





TEST NUMBER: P789869

CATALOG NUMBER: LER6D15D010-EC6DR600215IC9035-6LBDP1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93																
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86			86																
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80			80																
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75			75																
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			70																
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66			66																
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62			62																
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59			59																
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			55																
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53			53																

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	263690
5°	270170
10°	273438
15°	260481
20°	229662
25°	185765
30°	125646
35°	62970
40°	10212
45°	9997
50°	10199
55°	10344
60°	10642
65°	10884
70°	11149
75°	11271
80°	10885
85°	9026

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 75°  
 Luminance: 11271 cd/sqm



TEST NUMBER: P789869

CATALOG NUMBER: LER6D15D010-EC6DR600215IC9035-6LBDP1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	235.4	11.6
10°-20°	637.0	31.3
20°-30°	685.3	33.7
30°-40°	297.9	14.7
40°-50°	50.0	2.5
50°-60°	48.7	2.4
60°-70°	41.6	2.0
70°-80°	27.9	1.4
80°-90°	8.3	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1557.7	76.7
0°-40°	1855.6	91.3
0°-60°	1954.3	96.2
0°-90°	2032.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2032.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2413	
5°	2463	235
15°	2303	637
25°	1541	685
35°	472	298
45°	65	50
55°	54	49
65°	42	42
75°	27	28
85°	7	8
90°	0	



TEST NUMBER: P789869

CATALOG NUMBER: LER6D15D010-EC6DR600215IC9035-6LBDP1B

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2413.4
2.5°	2481.2
5°	2463.3
7.5°	2469.0
10°	2464.6
12.5°	2413.7
15°	2302.8
17.5°	2153.9
20°	1975.2
22.5°	1784.0
25°	1540.9
27.5°	1232.4
30°	995.9
32.5°	767.6
35°	472.1
37.5°	202.0
40°	71.6
42.5°	66.0
45°	64.7
47.5°	62.5
50°	60.0
52.5°	57.2
55°	54.3
57.5°	51.5
60°	48.7
62.5°	45.5
65°	42.1
67.5°	38.6
70°	34.9
72.5°	30.8
75°	26.7
77.5°	22.0
80°	17.3
82.5°	12.2
85°	7.2
87.5°	2.5
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)