

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P789885

Luminaire Tested: LER6D15D010-EC6DR600215IC9050-6LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P789885
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D15D010-EC6DR600215IC9050-6LBDP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2751.6 lumens
Efficiency: N/A
Efficacy: 174.2 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P789885

CATALOG NUMBER: LER6D15D010-EC6DR600215IC9050-6LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P789885

CATALOG NUMBER: LER6D15D010-EC6DR600215IC9050-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	357053
5°	365831
10°	370250
15°	352715
20°	310983
25°	251540
30°	170144
35°	85258
40°	13835
45°	13536
50°	13802
55°	14020
60°	14401
65°	14736
70°	15078
75°	15240
80°	14723
85°	12286

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 15240 cd/sqm



TEST NUMBER: P789885

CATALOG NUMBER: LER6D15D010-EC6DR600215IC9050-6LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	318.8	11.6
10°-20°	862.5	31.3
20°-30°	928.0	33.7
30°-40°	403.4	14.7
40°-50°	67.7	2.5
50°-60°	65.9	2.4
60°-70°	56.3	2.0
70°-80°	37.7	1.4
80°-90°	11.3	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2109.3	76.7
0°-40°	2512.7	91.3
0°-60°	2646.3	96.2
0°-90°	2751.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2751.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3268	
5°	3336	319
15°	3118	863
25°	2086	928
35°	639	403
45°	88	68
55°	74	66
65°	57	56
75°	36	38
85°	10	11
90°	0	



TEST NUMBER: P789885

CATALOG NUMBER: LER6D15D010-EC6DR600215IC9050-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	3267.9
2.5°	3359.8
5°	3335.5
7.5°	3343.2
10°	3337.2
12.5°	3268.3
15°	3118.2
17.5°	2916.6
20°	2674.6
22.5°	2415.6
25°	2086.5
27.5°	1668.8
30°	1348.6
32.5°	1039.4
35°	639.2
37.5°	273.5
40°	97.0
42.5°	89.3
45°	87.6
47.5°	84.6
50°	81.2
52.5°	77.4
55°	73.6
57.5°	69.7
60°	65.9
62.5°	61.7
65°	57.0
67.5°	52.3
70°	47.2
72.5°	41.7
75°	36.1
77.5°	29.8
80°	23.4
82.5°	16.6
85°	9.8
87.5°	3.4
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)