

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P789909

Luminaire Tested: LER6D15D010-EC6DR650215IC9030-6LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P789909
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D15D010-EC6DR650215IC9030-6LBDP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2242.6 lumens
Efficiency: N/A
Efficacy: 141.9 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P789909
CATALOG NUMBER: LER6D15D010-EC6DR650215IC9030-6LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P789909

CATALOG NUMBER: LER6D15D010-EC6DR650215IC9030-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87																			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80																			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69																			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65																			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60																			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57																			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53																			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	241259
5°	241456
10°	249951
15°	250369
20°	230511
25°	196398
30°	150349
35°	106226
40°	62700
45°	25449
50°	9230
55°	5143
60°	2950
65°	1629
70°	1693
75°	1309
80°	1384
85°	1128

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 25449 cd/sqm



TEST NUMBER: P789909

CATALOG NUMBER: LER6D15D010-EC6DR650215IC9030-6LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	212.6	9.5
10°-20°	613.3	27.3
20°-30°	735.9	32.8
30°-40°	494.5	22.1
40°-50°	148.0	6.6
50°-60°	26.2	1.2
60°-70°	7.4	0.3
70°-80°	3.6	0.2
80°-90°	1.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1561.8	69.6
0°-40°	2056.3	91.7
0°-60°	2230.5	99.5
0°-90°	2242.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2242.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2208	
5°	2202	213
15°	2213	613
25°	1629	736
35°	796	495
45°	165	148
55°	27	26
65°	6	7
75°	3	4
85°	1	1
90°	0	



TEST NUMBER: P789909

CATALOG NUMBER: LER6D15D010-EC6DR650215IC9030-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	2208.1
2.5°	2217.5
5°	2201.5
7.5°	2234.7
10°	2252.9
12.5°	2248.5
15°	2213.4
17.5°	2127.4
20°	1982.5
22.5°	1811.8
25°	1629.1
27.5°	1423.0
30°	1191.7
32.5°	982.1
35°	796.4
37.5°	612.8
40°	439.6
42.5°	287.1
45°	164.7
47.5°	87.2
50°	54.3
52.5°	37.7
55°	27.0
57.5°	19.5
60°	13.5
62.5°	8.8
65°	6.3
67.5°	5.6
70°	5.3
72.5°	4.1
75°	3.1
77.5°	2.8
80°	2.2
82.5°	1.6
85°	0.9
87.5°	0.6
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)