

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P791152

Luminaire Tested: LER6D25D010-EC6DR7020359030-6LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P791152
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D25D010-EC6DR7020359030-6LBDP1H
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4995.6 lumens
Efficiency: N/A
Efficacy: 199.0 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 25.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P791152

CATALOG NUMBER: LER6D25D010-EC6DR7020359030-6LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P791152

CATALOG NUMBER: LER6D25D010-EC6DR7020359030-6LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	613663
5°	595421
10°	578829
15°	571231
20°	533413
25°	400728
30°	283275
35°	100344
40°	52759
45°	56198
50°	58201
55°	59281
60°	59656
65°	58403
70°	55106
75°	51038
80°	45303
85°	36731

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 59684 cd/sqm



TEST NUMBER: P791152

CATALOG NUMBER: LER6D25D010-EC6DR7020359030-6LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	512.1	10.3
10°-20°	1404.5	28.1
20°-30°	1546.9	31.0
30°-40°	591.0	11.8
40°-50°	279.1	5.6
50°-60°	277.4	5.6
60°-70°	222.1	4.4
70°-80°	127.6	2.6
80°-90°	34.7	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3463.5	69.3
0°-40°	4054.6	81.2
0°-60°	4611.1	92.3
0°-90°	4995.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4995.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5616	
5°	5429	512
15°	5050	1405
25°	3324	1547
35°	752	591
45°	364	279
55°	311	277
65°	226	222
75°	121	128
85°	29	35
90°	0	



TEST NUMBER: P791152

CATALOG NUMBER: LER6D25D010-EC6DR7020359030-6LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	5616.5
2.5°	5557.8
5°	5428.8
7.5°	5321.2
10°	5217.2
12.5°	5129.2
15°	5050.0
17.5°	4858.8
20°	4587.6
22.5°	4002.5
25°	3324.0
27.5°	2893.6
30°	2245.3
32.5°	1450.4
35°	752.3
37.5°	406.4
40°	369.9
42.5°	367.3
45°	363.7
47.5°	355.7
50°	342.4
52.5°	327.2
55°	311.2
57.5°	293.5
60°	273.0
62.5°	249.9
65°	225.9
67.5°	199.2
70°	172.5
72.5°	145.8
75°	120.9
77.5°	95.1
80°	72.0
82.5°	50.7
85°	29.3
87.5°	11.6
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)