

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P791153

Luminaire Tested: LER6D25D010-EC6DR7020359030-6LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P791153
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D25D010-EC6DR7020359030-6LBDDP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5245.3 lumens
Efficiency: N/A
Efficacy: 209.0 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 25.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P791153
CATALOG NUMBER: LER6D25D010-EC6DR7020359030-6LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P791153
 CATALOG NUMBER: LER6D25D010-EC6DR7020359030-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	644343
5°	625198
10°	607775
15°	599793
20°	560086
25°	420764
30°	297443
35°	105359
40°	55397
45°	59010
50°	61108
55°	62252
60°	62628
65°	61324
70°	57854
75°	53613
80°	47568
85°	38612

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 62653 cd/sqm



TEST NUMBER: P791153

CATALOG NUMBER: LER6D25D010-EC6DR7020359030-6LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	537.7	10.3
10°-20°	1474.8	28.1
20°-30°	1624.3	31.0
30°-40°	620.6	11.8
40°-50°	293.0	5.6
50°-60°	291.3	5.6
60°-70°	233.3	4.4
70°-80°	134.0	2.6
80°-90°	36.4	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3636.7	69.3
0°-40°	4257.3	81.2
0°-60°	4841.6	92.3
0°-90°	5245.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5245.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5897	
5°	5700	538
15°	5302	1475
25°	3490	1624
35°	790	621
45°	382	293
55°	327	291
65°	237	233
75°	127	134
85°	31	36
90°	0	



TEST NUMBER: P791153

CATALOG NUMBER: LER6D25D010-EC6DR7020359030-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	5897.3
2.5°	5835.7
5°	5700.3
7.5°	5587.3
10°	5478.1
12.5°	5385.6
15°	5302.5
17.5°	5101.8
20°	4817.0
22.5°	4202.6
25°	3490.2
27.5°	3038.3
30°	2357.6
32.5°	1522.9
35°	789.9
37.5°	426.7
40°	388.4
42.5°	385.6
45°	381.9
47.5°	373.5
50°	359.5
52.5°	343.6
55°	326.8
57.5°	308.1
60°	286.6
62.5°	262.4
65°	237.2
67.5°	209.2
70°	181.1
72.5°	153.1
75°	127.0
77.5°	99.9
80°	75.6
82.5°	53.2
85°	30.8
87.5°	12.1
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)