

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P789945

Luminaire Tested: LER6D15D010-EC6DR700215IC9027-6LBDP1B

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P789945  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D15D010-EC6DR700215IC9027-6LBDP1B  
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1386.4 lumens  
Efficiency: N/A  
Efficacy: 87.7 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 15.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P789945

CATALOG NUMBER: LER6D15D010-EC6DR700215IC9027-6LBDP1B

### Luminous Intensity Polar Plot





TEST NUMBER: P789945

CATALOG NUMBER: LER6D15D010-EC6DR700215IC9027-6LBDP1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	170305
5°	165252
10°	160639
15°	158531
20°	148039
25°	111213
30°	78612
35°	27850
40°	14648
45°	15591
50°	16148
55°	16458
60°	16564
65°	16210
70°	15302
75°	14184
80°	12584
85°	10154

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 60°  
 Luminance: 16564 cd/sqm



TEST NUMBER: P789945

CATALOG NUMBER: LER6D15D010-EC6DR700215IC9027-6LBDP1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	142.1	10.3
10°-20°	389.8	28.1
20°-30°	429.3	31.0
30°-40°	164.0	11.8
40°-50°	77.4	5.6
50°-60°	77.0	5.6
60°-70°	61.7	4.4
70°-80°	35.5	2.6
80°-90°	9.6	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	961.2	69.3
0°-40°	1125.3	81.2
0°-60°	1279.7	92.3
0°-90°	1386.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1386.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1559	
5°	1507	142
15°	1402	390
25°	922	429
35°	209	164
45°	101	77
55°	86	77
65°	63	62
75°	34	35
85°	8	10
90°	0	



TEST NUMBER: P789945

CATALOG NUMBER: LER6D15D010-EC6DR700215IC9027-6LBDP1B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1558.7
2.5°	1542.4
5°	1506.7
7.5°	1476.8
10°	1447.9
12.5°	1423.5
15°	1401.5
17.5°	1348.5
20°	1273.2
22.5°	1110.8
25°	922.5
27.5°	803.1
30°	623.1
32.5°	402.5
35°	208.8
37.5°	112.8
40°	102.7
42.5°	101.9
45°	100.9
47.5°	98.7
50°	95.0
52.5°	90.8
55°	86.4
57.5°	81.4
60°	75.8
62.5°	69.3
65°	62.7
67.5°	55.3
70°	47.9
72.5°	40.5
75°	33.6
77.5°	26.4
80°	20.0
82.5°	14.1
85°	8.1
87.5°	3.2
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)