

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P791161

Luminaire Tested: LER6D25D010-EC6DR7020359035-6LBDP1LI

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P791161  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D25D010-EC6DR7020359035-6LB DP1LI  
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5537.4 lumens  
Efficiency: N/A  
Efficacy: 220.6 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 25.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P791161  
CATALOG NUMBER: LER6D25D010-EC6DR7020359035-6LBDP1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P791161  
 CATALOG NUMBER: LER6D25D010-EC6DR7020359035-6LBDP1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	680214
5°	659999
10°	641613
15°	633184
20°	591271
25°	444188
30°	314008
35°	111228
40°	58478
45°	62286
50°	64507
55°	65719
60°	66125
65°	64737
70°	61080
75°	56610
80°	50211
85°	40743

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 57.5°  
 Luminance: 66150 cd/sqm



TEST NUMBER: P791161

CATALOG NUMBER: LER6D25D010-EC6DR7020359035-6LBDP1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	567.6	10.3
10°-20°	1556.9	28.1
20°-30°	1714.7	31.0
30°-40°	655.1	11.8
40°-50°	309.3	5.6
50°-60°	307.5	5.6
60°-70°	246.2	4.4
70°-80°	141.5	2.6
80°-90°	38.5	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3839.2	69.3
0°-40°	4494.3	81.2
0°-60°	5111.2	92.3
0°-90°	5537.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5537.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6226	
5°	6018	568
15°	5598	1557
25°	3684	1715
35°	834	655
45°	403	309
55°	345	308
65°	250	246
75°	134	142
85°	32	38
90°	0	



TEST NUMBER: P791161

CATALOG NUMBER: LER6D25D010-EC6DR7020359035-6LBDP1LI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	6225.6
2.5°	6160.6
5°	6017.6
7.5°	5898.4
10°	5783.1
12.5°	5685.5
15°	5597.7
17.5°	5385.8
20°	5085.2
22.5°	4436.6
25°	3684.5
27.5°	3207.4
30°	2488.9
32.5°	1607.7
35°	833.9
37.5°	450.5
40°	410.0
42.5°	407.1
45°	403.1
47.5°	394.3
50°	379.5
52.5°	362.7
55°	345.0
57.5°	325.3
60°	302.6
62.5°	277.0
65°	250.4
67.5°	220.8
70°	191.2
72.5°	161.7
75°	134.1
77.5°	105.5
80°	79.8
82.5°	56.2
85°	32.5
87.5°	12.8
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)