

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P791175

Luminaire Tested: LER6D25D010-EC6DR7020359050-6LBDP1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P791175
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D25D010-EC6DR7020359050-6LBDDP1B
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3116.0 lumens
Efficiency: N/A
Efficacy: 124.1 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 25.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P791175
CATALOG NUMBER: LER6D25D010-EC6DR7020359050-6LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P791175

CATALOG NUMBER: LER6D25D010-EC6DR7020359050-6LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	382773
5°	371403
10°	361052
15°	356312
20°	332715
25°	249961
30°	176692
35°	62597
40°	32905
45°	35060
50°	36291
55°	36974
60°	37214
65°	36427
70°	34374
75°	31830
80°	28251
85°	22941

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 60°
 Luminance: 37214 cd/sqm



TEST NUMBER: P791175

CATALOG NUMBER: LER6D25D010-EC6DR7020359050-6LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	319.4	10.3
10°-20°	876.1	28.1
20°-30°	964.9	31.0
30°-40°	368.7	11.8
40°-50°	174.1	5.6
50°-60°	173.0	5.6
60°-70°	138.6	4.4
70°-80°	79.6	2.6
80°-90°	21.6	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2160.4	69.3
0°-40°	2529.1	81.2
0°-60°	2876.2	92.3
0°-90°	3116.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3116.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3503	
5°	3386	319
15°	3150	876
25°	2073	965
35°	469	369
45°	227	174
55°	194	173
65°	141	139
75°	75	80
85°	18	22
90°	0	



TEST NUMBER: P791175

CATALOG NUMBER: LER6D25D010-EC6DR7020359050-6LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	3503.3
2.5°	3466.7
5°	3386.3
7.5°	3319.2
10°	3254.3
12.5°	3199.3
15°	3150.0
17.5°	3030.7
20°	2861.5
22.5°	2496.6
25°	2073.4
27.5°	1804.9
30°	1400.5
32.5°	904.7
35°	469.3
37.5°	253.5
40°	230.7
42.5°	229.1
45°	226.9
47.5°	221.9
50°	213.5
52.5°	204.1
55°	194.1
57.5°	183.0
60°	170.3
62.5°	155.9
65°	140.9
67.5°	124.2
70°	107.6
72.5°	91.0
75°	75.4
77.5°	59.3
80°	44.9
82.5°	31.6
85°	18.3
87.5°	7.2
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)