

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P789948

Luminaire Tested: LER6D15D010-EC6DR700215IC9027-6LBDP1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P789948
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D15D010-EC6DR700215IC9027-6LBDP1MW
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1861.2 lumens
Efficiency: N/A
Efficacy: 117.8 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P789948

CATALOG NUMBER: LER6D15D010-EC6DR700215IC9027-6LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P789948

CATALOG NUMBER: LER6D15D010-EC6DR700215IC9027-6LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	228639
5°	221846
10°	215657
15°	212826
20°	198734
25°	149308
30°	105548
35°	37387
40°	19654
45°	20937
50°	21689
55°	22097
60°	22224
65°	21768
70°	20541
75°	19039
80°	16863
85°	13665

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 22226 cd/sqm



TEST NUMBER: P789948

CATALOG NUMBER: LER6D15D010-EC6DR700215IC9027-6LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	190.8	10.3
10°-20°	523.3	28.1
20°-30°	576.4	31.0
30°-40°	220.2	11.8
40°-50°	104.0	5.6
50°-60°	103.4	5.6
60°-70°	82.8	4.4
70°-80°	47.6	2.6
80°-90°	12.9	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1290.4	69.3
0°-40°	1510.6	81.2
0°-60°	1718.0	92.3
0°-90°	1861.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1861.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2093	
5°	2023	191
15°	1882	523
25°	1238	576
35°	280	220
45°	136	104
55°	116	103
65°	84	83
75°	45	48
85°	11	13
90°	0	



TEST NUMBER: P789948

CATALOG NUMBER: LER6D15D010-EC6DR700215IC9027-6LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2092.6
2.5°	2070.7
5°	2022.7
7.5°	1982.6
10°	1943.8
12.5°	1911.0
15°	1881.5
17.5°	1810.3
20°	1709.2
22.5°	1491.2
25°	1238.5
27.5°	1078.1
30°	836.6
32.5°	540.4
35°	280.3
37.5°	151.4
40°	137.8
42.5°	136.8
45°	135.5
47.5°	132.5
50°	127.6
52.5°	121.9
55°	116.0
57.5°	109.3
60°	101.7
62.5°	93.1
65°	84.2
67.5°	74.2
70°	64.3
72.5°	54.3
75°	45.1
77.5°	35.5
80°	26.8
82.5°	18.9
85°	10.9
87.5°	4.3
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)