

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P789963

Luminaire Tested: LER6D15D010-EC6DR700215IC9035-6LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P789963
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D15D010-EC6DR700215IC9035-6LBDP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2727.3 lumens
Efficiency: N/A
Efficacy: 172.6 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P789963

CATALOG NUMBER: LER6D15D010-EC6DR700215IC9035-6LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P789963

CATALOG NUMBER: LER6D15D010-EC6DR700215IC9035-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	335026
5°	325075
10°	316008
15°	311858
20°	291217
25°	218773
30°	154651
35°	54780
40°	28811
45°	30687
50°	31769
55°	32364
60°	32560
65°	31877
70°	30093
75°	27862
80°	24728
85°	20058

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 32577 cd/sqm



TEST NUMBER: P789963

CATALOG NUMBER: LER6D15D010-EC6DR700215IC9035-6LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	279.6	10.3
10°-20°	766.8	28.1
20°-30°	844.5	31.0
30°-40°	322.7	11.8
40°-50°	152.4	5.6
50°-60°	151.5	5.6
60°-70°	121.2	4.4
70°-80°	69.7	2.6
80°-90°	18.9	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1890.9	69.3
0°-40°	2213.6	81.2
0°-60°	2517.4	92.3
0°-90°	2727.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2727.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3066	
5°	2964	280
15°	2757	767
25°	1815	845
35°	411	323
45°	199	152
55°	170	151
65°	123	121
75°	66	70
85°	16	19
90°	0	



TEST NUMBER: P789963

CATALOG NUMBER: LER6D15D010-EC6DR700215IC9035-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	3066.3
2.5°	3034.2
5°	2963.9
7.5°	2905.1
10°	2848.3
12.5°	2800.2
15°	2757.0
17.5°	2652.7
20°	2504.6
22.5°	2185.1
25°	1814.7
27.5°	1579.8
30°	1225.8
32.5°	791.8
35°	410.7
37.5°	221.9
40°	202.0
42.5°	200.5
45°	198.6
47.5°	194.2
50°	186.9
52.5°	178.7
55°	169.9
57.5°	160.2
60°	149.0
62.5°	136.4
65°	123.3
67.5°	108.7
70°	94.2
72.5°	79.6
75°	66.0
77.5°	51.9
80°	39.3
82.5°	27.7
85°	16.0
87.5°	6.3
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)