

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P789993

Luminaire Tested: LER6D20D010-EC6DR1015209027-6LBDP1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P789993
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D20D010-EC6DR1015209027-6LBDDP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 10° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1930.5 lumens
Efficiency: N/A
Efficacy: 83.6 lumens/watt
Spacing Criteria (0/90/45): 0.17 / 0.17 / 0.18
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 23.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P789993
CATALOG NUMBER: LER6D20D010-EC6DR1015209027-6LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P789993

CATALOG NUMBER: LER6D20D010-EC6DR1015209027-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|----|----|-----|--|--|--|----|--|--|--|--|--|--|--|--|---|
| RF | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | |
| RC | 80 | | | | | | | | | 50 | | | | | | | | | 30 | | | | | | | | | 10 | | | | | | | | | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | | | | | | | | | | | | | |
| RCR | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | | | | 100 | | | | | | | | | | | | | |
| 1 | 116 | 114 | 113 | 111 | 114 | 112 | 111 | 109 | 108 | 107 | 106 | 104 | 104 | 103 | 101 | 101 | 100 | 98 | | | | | | 98 | | | | | | | | | | | | | |
| 2 | 113 | 110 | 108 | 106 | 111 | 108 | 106 | 104 | 105 | 104 | 102 | 103 | 101 | 100 | 100 | 99 | 98 | 97 | | | | | | 97 | | | | | | | | | | | | | |
| 3 | 111 | 107 | 104 | 102 | 109 | 106 | 103 | 101 | 103 | 101 | 99 | 101 | 99 | 98 | 99 | 98 | 96 | 95 | | | | | | 95 | | | | | | | | | | | | | |
| 4 | 108 | 104 | 101 | 99 | 107 | 103 | 100 | 98 | 101 | 99 | 97 | 99 | 97 | 96 | 98 | 96 | 95 | 94 | | | | | | 94 | | | | | | | | | | | | | |
| 5 | 106 | 102 | 99 | 96 | 105 | 101 | 98 | 96 | 99 | 97 | 95 | 98 | 96 | 94 | 97 | 95 | 94 | 93 | | | | | | 93 | | | | | | | | | | | | | |
| 6 | 104 | 100 | 96 | 94 | 103 | 99 | 96 | 94 | 98 | 95 | 93 | 97 | 94 | 93 | 96 | 94 | 92 | 91 | | | | | | 91 | | | | | | | | | | | | | |
| 7 | 103 | 98 | 95 | 93 | 102 | 97 | 94 | 92 | 96 | 94 | 92 | 95 | 93 | 92 | 95 | 93 | 91 | 90 | | | | | | 90 | | | | | | | | | | | | | |
| 8 | 101 | 96 | 93 | 91 | 100 | 96 | 93 | 91 | 95 | 92 | 91 | 94 | 92 | 90 | 93 | 92 | 90 | 89 | | | | | | 89 | | | | | | | | | | | | | |
| 9 | 100 | 95 | 92 | 90 | 99 | 94 | 92 | 90 | 94 | 91 | 90 | 93 | 91 | 89 | 93 | 91 | 89 | 88 | | | | | | 88 | | | | | | | | | | | | | |
| 10 | 98 | 94 | 91 | 89 | 98 | 93 | 91 | 89 | 93 | 90 | 88 | 92 | 90 | 88 | 92 | 90 | 88 | 87 | | | | | | 87 | | | | | | | | | | | | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|---------|
| | 0° |
| 0° | 4592525 |
| 5° | 2177758 |
| 10° | 446625 |
| 15° | 122617 |
| 20° | 49416 |
| 25° | 26486 |
| 30° | 15670 |
| 35° | 10190 |
| 40° | 6818 |
| 45° | 4435 |
| 50° | 2431 |
| 55° | 1829 |
| 60° | 1049 |
| 65° | 0 |
| 70° | 0 |
| 75° | 0 |
| 80° | 0 |
| 85° | 0 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4435 cd/sqm



TEST NUMBER: P789993

CATALOG NUMBER: LER6D20D010-EC6DR1015209027-6LBDP1LI

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 1372.7 | 71.1 |
| 10°-20° | 371.5 | 19.2 |
| 20°-30° | 106.4 | 5.5 |
| 30°-40° | 48.6 | 2.5 |
| 40°-50° | 22.3 | 1.2 |
| 50°-60° | 7.4 | 0.4 |
| 60°-70° | 1.7 | 0.1 |
| 70°-80° | 0.0 | 0.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 1850.5 | 95.9 |
| 0°-40° | 1899.0 | 98.4 |
| 0°-60° | 1928.8 | 99.9 |
| 0°-90° | 1930.5 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 1930.5 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-------|------|
| 0° | 42033 | |
| 5° | 19856 | ### |
| 15° | 1084 | 371 |
| 25° | 220 | 106 |
| 35° | 76 | 49 |
| 45° | 29 | 22 |
| 55° | 10 | 7 |
| 65° | 0 | 2 |
| 75° | 0 | 0 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P789993

CATALOG NUMBER: LER6D20D010-EC6DR1015209027-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|---------|
| 0° | 42032.7 |
| 0.5° | 41669.8 |
| 1° | 40738.6 |
| 1.5° | 38943.0 |
| 2° | 36932.6 |
| 2.5° | 34277.5 |
| 3° | 31326.3 |
| 3.5° | 28470.7 |
| 4° | 25390.6 |
| 4.5° | 22554.0 |
| 5° | 19855.9 |
| 5.5° | 17411.0 |
| 6° | 15080.6 |
| 6.5° | 13032.0 |
| 7° | 11102.7 |
| 7.5° | 9455.2 |
| 8° | 7993.9 |
| 8.5° | 6714.2 |
| 9° | 5606.3 |
| 9.5° | 4761.0 |
| 10° | 4025.6 |
| 12.5° | 1919.7 |
| 15° | 1084.0 |
| 17.5° | 659.0 |
| 20° | 425.0 |
| 22.5° | 296.1 |
| 25° | 219.7 |
| 27.5° | 162.4 |
| 30° | 124.2 |
| 32.5° | 95.5 |
| 35° | 76.4 |
| 37.5° | 57.3 |
| 40° | 47.8 |
| 42.5° | 38.2 |
| 45° | 28.7 |
| 47.5° | 19.1 |
| 50° | 14.3 |
| 52.5° | 9.6 |
| 55° | 9.6 |
| 57.5° | 4.8 |
| 60° | 4.8 |
| 62.5° | 4.8 |
| 65° | 0.0 |



TEST NUMBER: P789993
CATALOG NUMBER: LER6D20D010-EC6DR1015209027-6LBDP1LI

CANDELA DISTRIBUTION (continued):

| | 0° |
|-------|-----|
| 72.5° | 0.0 |
| 75° | 0.0 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





| | | |
|-------|--|-----|
| 67.5° | | 0.0 |
| 70° | | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)