

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P791261

Luminaire Tested: LER6D30D010-EC6DR2015309035-6LBS1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P791261
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D30D010-EC6DR2015309035-6LBS1LI
Description: 6 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 20° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3940.6 lumens
Efficiency: N/A
Efficacy: 135.9 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 29
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P791261
CATALOG NUMBER: LER6D30D010-EC6DR2015309035-6LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P791261

CATALOG NUMBER: LER6D30D010-EC6DR2015309035-6LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	97	97	97																
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94	94	94	94																
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91	91	91	91																
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88	88	88	88																
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85	85	85	85																
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83	83	83	83																
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81	81	81	81																
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79	79	79	79																
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77	77	77	77																
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	75	75	75	75																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2450566
5°	2210869
10°	1240856
15°	630752
20°	267056
25°	123280
30°	65264
35°	35160
40°	18799
45°	11110
50°	6442
55°	3429
60°	2185
65°	1551
70°	639
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 11110 cd/sqm



TEST NUMBER: P791261

CATALOG NUMBER: LER6D30D010-EC6DR2015309035-6LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1596.9	40.5
10°-20°	1572.4	39.9
20°-30°	513.7	13.0
30°-40°	174.9	4.4
40°-50°	58.8	1.5
50°-60°	17.7	0.4
60°-70°	5.9	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3683.0	93.5
0°-40°	3857.9	97.9
0°-60°	3934.4	99.8
0°-90°	3940.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3940.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	22429	
5°	20158	###
15°	5576	1572
25°	1023	514
35°	264	175
45°	72	59
55°	18	18
65°	6	6
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P791261

CATALOG NUMBER: LER6D30D010-EC6DR2015309035-6LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	22428.6
0.5°	22428.6
1°	22400.6
1.5°	22344.7
2°	22242.8
2.5°	22107.0
3°	21915.3
3.5°	21647.7
4°	21250.2
4.5°	20766.9
5°	20157.8
5.5°	19356.9
6°	18536.0
6.5°	17595.3
7°	16674.6
7.5°	15596.1
8°	14633.5
8.5°	13664.8
9°	12770.1
9.5°	11949.3
10°	11184.3
12.5°	8030.7
15°	5576.2
17.5°	3642.9
20°	2296.8
22.5°	1487.9
25°	1022.6
27.5°	719.0
30°	517.3
32.5°	371.5
35°	263.6
37.5°	183.7
40°	131.8
42.5°	95.9
45°	71.9
47.5°	55.9
50°	37.9
52.5°	24.0
55°	18.0
57.5°	14.0
60°	10.0
62.5°	8.0
65°	6.0



TEST NUMBER: P791261
CATALOG NUMBER: LER6D30D010-EC6DR2015309035-6LBS1LI

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



67.5°		4.0
70°		2.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)