

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P791268

Luminaire Tested: LER6D30D010-EC6DR2015309040-6LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P791268
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D30D010-EC6DR2015309040-6LBS1H
Description: 6 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 20° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3856.7 lumens
Efficiency: N/A
Efficacy: 133.0 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 29
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P791268

CATALOG NUMBER: LER6D30D010-EC6DR2015309040-6LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P791268

CATALOG NUMBER: LER6D30D010-EC6DR2015309040-6LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	97	98	97																
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94	94	98	94																
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91	91	98	91																
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88	88	93	89																
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85	85	91	86																
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83	83	88	84																
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81	81	86	82																
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79	79	84	80																
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77	77	82	78																
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	75	75	81	76																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2398405
5°	2163807
10°	1214451
15°	617325
20°	261370
25°	120652
30°	63877
35°	34413
40°	18399
45°	10878
50°	6306
55°	3353
60°	2142
65°	1525
70°	639
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 10878 cd/sqm



TEST NUMBER: P791268

CATALOG NUMBER: LER6D30D010-EC6DR2015309040-6LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1562.9	40.5
10°-20°	1538.9	39.9
20°-30°	502.8	13.0
30°-40°	171.2	4.4
40°-50°	57.5	1.5
50°-60°	17.3	0.4
60°-70°	5.8	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3604.6	93.5
0°-40°	3775.8	97.9
0°-60°	3850.6	99.8
0°-90°	3856.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3856.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	21951	
5°	19729	###
15°	5458	1539
25°	1001	503
35°	258	171
45°	70	58
55°	18	17
65°	6	6
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P791268

CATALOG NUMBER: LER6D30D010-EC6DR2015309040-6LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	21951.2
0.5°	21951.2
1°	21923.8
1.5°	21869.1
2°	21769.4
2.5°	21636.4
3°	21448.8
3.5°	21186.9
4°	20797.9
4.5°	20324.9
5°	19728.7
5.5°	18944.8
6°	18141.5
6.5°	17220.8
7°	16319.7
7.5°	15264.2
8°	14322.0
8.5°	13374.0
9°	12498.3
9.5°	11694.9
10°	10946.3
12.5°	7859.8
15°	5457.5
17.5°	3565.4
20°	2247.9
22.5°	1456.2
25°	1000.8
27.5°	703.7
30°	506.3
32.5°	363.6
35°	258.0
37.5°	179.8
40°	129.0
42.5°	93.8
45°	70.4
47.5°	54.7
50°	37.1
52.5°	23.5
55°	17.6
57.5°	13.7
60°	9.8
62.5°	7.8
65°	5.9



TEST NUMBER: P791268
CATALOG NUMBER: LER6D30D010-EC6DR2015309040-6LBS1H

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



67.5°		3.9
70°		2.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)