

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P791275

Luminaire Tested: LER6D30D010-EC6DR2015309050-6LBS1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P791275
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D30D010-EC6DR2015309050-6LBS1B
Description: 6 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 20° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3566.4 lumens
Efficiency: N/A
Efficacy: 123.0 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 29
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P791275
CATALOG NUMBER: LER6D30D010-EC6DR2015309050-6LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P791275

CATALOG NUMBER: LER6D30D010-EC6DR2015309050-6LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	97	98	98	97															
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94	94	98	96	95															
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91	91	98	96	95															
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88	88	93	91	89															
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85	85	91	88	86															
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83	83	88	86	84															
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81	81	86	84	82															
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79	79	84	82	80															
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77	77	82	80	78															
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	75	75	81	78	76															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2217884
5°	2000946
10°	1123043
15°	570858
20°	241696
25°	111574
30°	59070
35°	31825
40°	17016
45°	10059
50°	5830
55°	3105
60°	1967
65°	1396
70°	575
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 10059 cd/sqm



TEST NUMBER: P791275

CATALOG NUMBER: LER6D30D010-EC6DR2015309050-6LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1445.3	40.5
10°-20°	1423.1	39.9
20°-30°	464.9	13.0
30°-40°	158.3	4.4
40°-50°	53.2	1.5
50°-60°	16.0	0.4
60°-70°	5.3	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3333.3	93.5
0°-40°	3491.6	97.9
0°-60°	3560.8	99.8
0°-90°	3566.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3566.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	20299	
5°	18244	###
15°	5047	1423
25°	926	465
35°	239	158
45°	65	53
55°	16	16
65°	5	5
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P791275
CATALOG NUMBER: LER6D30D010-EC6DR2015309050-6LBS1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	20299.0
0.5°	20299.0
1°	20273.7
1.5°	20223.1
2°	20130.9
2.5°	20008.0
3°	19834.5
3.5°	19592.3
4°	19232.6
4.5°	18795.1
5°	18243.8
5.5°	17519.0
6°	16776.1
6.5°	15924.7
7°	15091.4
7.5°	14115.3
8°	13244.1
8.5°	12367.4
9°	11557.6
9.5°	10814.7
10°	10122.4
12.5°	7268.2
15°	5046.7
17.5°	3297.0
20°	2078.7
22.5°	1346.6
25°	925.5
27.5°	650.7
30°	468.2
32.5°	336.2
35°	238.6
37.5°	166.3
40°	119.3
42.5°	86.8
45°	65.1
47.5°	50.6
50°	34.3
52.5°	21.7
55°	16.3
57.5°	12.7
60°	9.0
62.5°	7.2
65°	5.4



TEST NUMBER: P791275

CATALOG NUMBER: LER6D30D010-EC6DR2015309050-6LBS1B

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



67.5°		3.6
70°		1.8

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)