

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P791277

Luminaire Tested: LER6D30D010-EC6DR2015309050-6LBS1LI

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P791277  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D30D010-EC6DR2015309050-6LBS1LI  
Description: 6 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 20° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4001.7 lumens  
Efficiency: N/A  
Efficacy: 138.0 lumens/watt  
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 29  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P791277

CATALOG NUMBER: LER6D30D010-EC6DR2015309050-6LBS1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P791277

CATALOG NUMBER: LER6D30D010-EC6DR2015309050-6LBS1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	97	98	97																
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94	94	98	94																
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91	91	95	91																
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88	88	93	89																
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85	85	91	86																
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83	83	88	84																
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81	81	86	82																
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79	79	84	80																
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77	77	82	78																
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	75	75	81	76																

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	2488621
5°	2245199
10°	1260128
15°	640548
20°	271206
25°	125185
30°	66274
35°	35707
40°	19098
45°	11280
50°	6544
55°	3486
60°	2207
65°	1577
70°	639
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 11280 cd/sqm



TEST NUMBER: P791277

CATALOG NUMBER: LER6D30D010-EC6DR2015309050-6LBS1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1621.7	40.5
10°-20°	1596.8	39.9
20°-30°	521.7	13.0
30°-40°	177.6	4.4
40°-50°	59.7	1.5
50°-60°	18.0	0.4
60°-70°	6.0	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3740.2	93.5
0°-40°	3917.8	97.9
0°-60°	3995.5	99.8
0°-90°	4001.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4001.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	22777	
5°	20471	###
15°	5663	1597
25°	1038	522
35°	268	178
45°	73	60
55°	18	18
65°	6	6
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P791277

CATALOG NUMBER: LER6D30D010-EC6DR2015309050-6LBS1LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	22776.9
0.5°	22776.9
1°	22748.5
1.5°	22691.7
2°	22588.3
2.5°	22450.4
3°	22255.7
3.5°	21983.9
4°	21580.3
4.5°	21089.4
5°	20470.8
5.5°	19657.5
6°	18823.9
6.5°	17868.6
7°	16933.6
7.5°	15838.4
8°	14860.8
8.5°	13877.1
9°	12968.4
9.5°	12134.8
10°	11358.0
12.5°	8155.5
15°	5662.8
17.5°	3699.5
20°	2332.5
22.5°	1511.0
25°	1038.4
27.5°	730.2
30°	525.3
32.5°	377.2
35°	267.7
37.5°	186.6
40°	133.9
42.5°	97.4
45°	73.0
47.5°	56.8
50°	38.5
52.5°	24.3
55°	18.3
57.5°	14.2
60°	10.1
62.5°	8.1
65°	6.1



TEST NUMBER: P791277

CATALOG NUMBER: LER6D30D010-EC6DR2015309050-6LBS1LI

**CANDELA DISTRIBUTION (continued):**

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



67.5°		4.1
70°		2.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)