

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P791306

Luminaire Tested: LER6D30D010-EC6DR2520359035-6LBDP1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P791306
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D30D010-EC6DR2520359035-6LB DP1MW
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 25° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4646.3 lumens
Efficiency: N/A
Efficacy: 160.2 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.45
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 29
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P791306

CATALOG NUMBER: LER6D30D010-EC6DR2520359035-6LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P791306

CATALOG NUMBER: LER6D30D010-EC6DR2520359035-6LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																												
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																												
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89																												
4	103	97	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85																												
5	100	93	89	86	98	93	89	86	91	87	85	89	86	84	88	85	83	82																												
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																												
7	93	87	82	79	92	86	82	79	85	81	78	84	80	78	83	80	78	77																												
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																												
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72																												
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69																												

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1925459
5°	1793325
10°	1279233
15°	753414
20°	468789
25°	257266
30°	117660
35°	44563
40°	20182
45°	12130
50°	5031
55°	3238
60°	2273
65°	1525
70°	224
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 12130 cd/sqm



TEST NUMBER: P791306

CATALOG NUMBER: LER6D30D010-EC6DR2520359035-6LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1405.2	30.2
10°-20°	1903.3	41.0
20°-30°	1007.2	21.7
30°-40°	248.6	5.4
40°-50°	60.6	1.3
50°-60°	15.9	0.3
60°-70°	5.3	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4315.7	92.9
0°-40°	4564.3	98.2
0°-60°	4640.9	99.9
0°-90°	4646.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4646.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	17623	
5°	16351	###
15°	6661	1903
25°	2134	1007
35°	334	249
45°	78	61
55°	17	16
65°	6	5
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P791306

CATALOG NUMBER: LER6D30D010-EC6DR2520359035-6LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	17622.6
2.5°	17333.0
5°	16350.8
7.5°	14377.5
10°	11530.2
12.5°	8716.1
15°	6660.6
17.5°	5191.0
20°	4031.8
22.5°	3023.6
25°	2134.0
27.5°	1431.1
30°	932.6
32.5°	567.4
35°	334.1
37.5°	204.4
40°	141.5
42.5°	108.1
45°	78.5
47.5°	47.4
50°	29.6
52.5°	21.5
55°	17.0
57.5°	13.3
60°	10.4
62.5°	8.1
65°	5.9
67.5°	2.2
70°	0.7
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)