

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P790121

Luminaire Tested: LER6D20D010-EC6DR2015309050-6LBDP1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P790121
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D20D010-EC6DR2015309050-6LBDDP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 20° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2287.6 lumens
Efficiency: N/A
Efficacy: 99.0 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 23.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P790121
CATALOG NUMBER: LER6D20D010-EC6DR2015309050-6LB DP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P790121

CATALOG NUMBER: LER6D20D010-EC6DR2015309050-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	97	97	97																
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94	94	94	94																
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91	91	91	91																
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88	88	88	88																
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85	85	85	85																
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83	83	83	83																
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81	81	81	81																
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79	79	79	79																
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77	77	77	77																
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	75	75	75	75																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1422597
5°	1283442
10°	720341
15°	366165
20°	155027
25°	71562
30°	37887
35°	20408
40°	10911
45°	6443
50°	3740
55°	1981
60°	1267
65°	905
70°	383
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 6443 cd/sqm



TEST NUMBER: P790121

CATALOG NUMBER: LER6D20D010-EC6DR2015309050-6LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	927.0	40.5
10°-20°	912.8	39.9
20°-30°	298.2	13.0
30°-40°	101.5	4.4
40°-50°	34.1	1.5
50°-60°	10.3	0.4
60°-70°	3.4	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2138.0	93.5
0°-40°	2239.6	97.9
0°-60°	2284.0	99.8
0°-90°	2287.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2287.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	13020	
5°	11702	927
15°	3237	913
25°	594	298
35°	153	102
45°	42	34
55°	10	10
65°	4	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P790121

CATALOG NUMBER: LER6D20D010-EC6DR2015309050-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	13020.2
0.5°	13020.2
1°	13004.0
1.5°	12971.5
2°	12912.4
2.5°	12833.5
3°	12722.2
3.5°	12566.9
4°	12336.1
4.5°	12055.6
5°	11701.9
5.5°	11237.0
6°	10760.5
6.5°	10214.4
7°	9679.9
7.5°	9053.8
8°	8495.0
8.5°	7932.7
9°	7413.3
9.5°	6936.8
10°	6492.7
12.5°	4662.0
15°	3237.1
17.5°	2114.8
20°	1333.3
22.5°	863.8
25°	593.6
27.5°	417.4
30°	300.3
32.5°	215.7
35°	153.0
37.5°	106.7
40°	76.5
42.5°	55.7
45°	41.7
47.5°	32.5
50°	22.0
52.5°	13.9
55°	10.4
57.5°	8.1
60°	5.8
62.5°	4.6
65°	3.5



TEST NUMBER: P790121
CATALOG NUMBER: LER6D20D010-EC6DR2015309050-6LBDP1LI

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





67.5°		2.3
70°		1.2

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)