

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P790126

Luminaire Tested: LER6D20D010-EC6DR2015309050-6LBS1MW

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P790126  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D20D010-EC6DR2015309050-6LBS1MW  
Description: 6 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 20° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2178.6 lumens  
Efficiency: N/A  
Efficacy: 94.3 lumens/watt  
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 23.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P790126  
CATALOG NUMBER: LER6D20D010-EC6DR2015309050-6LBS1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P790126  
 CATALOG NUMBER: LER6D20D010-EC6DR2015309050-6LBS1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97		
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94		
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91		
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88		
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85		
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83		
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81		
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79		
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77		
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	75		

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1354855
5°	1222330
10°	686036
15°	348722
20°	147643
25°	68162
30°	36083
35°	19447
40°	10398
45°	6150
50°	3570
55°	1886
60°	1202
65°	853
70°	351
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 6150 cd/sqm



TEST NUMBER: P790126

CATALOG NUMBER: LER6D20D010-EC6DR2015309050-6LBS1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	882.9	40.5
10°-20°	869.3	39.9
20°-30°	284.0	13.0
30°-40°	96.7	4.4
40°-50°	32.5	1.5
50°-60°	9.8	0.4
60°-70°	3.2	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2036.2	93.5
0°-40°	2132.9	97.9
0°-60°	2175.2	99.8
0°-90°	2178.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2178.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	12400	
5°	11145	883
15°	3083	869
25°	565	284
35°	146	97
45°	40	33
55°	10	10
65°	3	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P790126

CATALOG NUMBER: LER6D20D010-EC6DR2015309050-6LBS1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	12400.2
0.5°	12400.2
1°	12384.7
1.5°	12353.8
2°	12297.5
2.5°	12222.4
3°	12116.4
3.5°	11968.4
4°	11748.7
4.5°	11481.5
5°	11144.7
5.5°	10701.9
6°	10248.1
6.5°	9728.0
7°	9219.0
7.5°	8622.7
8°	8090.5
8.5°	7554.9
9°	7060.3
9.5°	6606.4
10°	6183.5
12.5°	4440.0
15°	3082.9
17.5°	2014.1
20°	1269.8
22.5°	822.6
25°	565.4
27.5°	397.5
30°	286.0
32.5°	205.4
35°	145.8
37.5°	101.6
40°	72.9
42.5°	53.0
45°	39.8
47.5°	30.9
50°	21.0
52.5°	13.3
55°	9.9
57.5°	7.7
60°	5.5
62.5°	4.4
65°	3.3



TEST NUMBER: P790126

CATALOG NUMBER: LER6D20D010-EC6DR2015309050-6LBS1MW

**CANDELA DISTRIBUTION (continued):**

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





67.5°		2.2
70°		1.1

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)