

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P791450

Luminaire Tested: LER6D30D010-EC6DR4020359035-6LB DP1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P791450
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D30D010-EC6DR4020359035-6LB DP1MW
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 40° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5816.0 lumens
Efficiency: N/A
Efficacy: 200.6 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 29
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P791450
CATALOG NUMBER: LER6D30D010-EC6DR4020359035-6LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P791450

CATALOG NUMBER: LER6D30D010-EC6DR4020359035-6LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	99	98	97	96	95	94	93	92	91	90	89	88													
	1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	97	96	95	94	93	92	91	90	89	88	87	86	85	84	83	82	81												
	2	110	106	103	100	108	105	102	99	102	99	97	99	97	95	96	95	93	92	91	90	89	88	87	86	85	84	83	82	81	80	79	78	77												
	3	106	101	97	94	104	100	96	93	97	94	92	95	93	90	93	91	89	88	87	86	85	84	83	82	81	80	79	78	77	76	75	74	73	72											
	4	102	97	92	89	101	95	91	88	93	90	87	92	89	86	90	87	85	84	83	82	81	80	79	78	77	76	75	74	73	72	71	70	69	68											
	5	99	92	88	84	97	91	87	84	90	86	83	88	85	83	87	84	82	81	80	79	78	77	76	75	74	73	72	71	70	69	68	67	66	65											
	6	95	88	84	80	94	88	83	80	86	82	80	85	82	79	84	81	79	77	76	75	74	73	72	71	70	69	68	67	66	65	64	63	62	61											
	7	92	85	80	77	91	84	80	77	83	79	76	82	79	76	81	78	76	74	73	72	71	70	69	68	67	66	65	64	63	62	61	60	59	58											
	8	89	82	77	74	88	81	77	74	80	76	73	79	76	73	78	75	73	72	71	70	69	68	67	66	65	64	63	62	61	60	59	58	57	56	55										
	9	86	79	74	71	85	78	74	71	77	73	71	76	73	70	76	72	70	69	68	67	66	65	64	63	62	61	60	59	58	57	56	55	54	53	52										
	10	83	76	71	68	82	75	71	68	75	71	68	74	70	68	73	70	68	67	66	65	64	63	62	61	60	59	58	57	56	55	54	53	52	51	50										

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1479522
5°	1472330
10°	1391677
15°	1183093
20°	806364
25°	336447
30°	105788
35°	49165
40°	27185
45°	12470
50°	6051
55°	3315
60°	1726
65°	620
70°	256
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 12470 cd/sqm



TEST NUMBER: P791450

CATALOG NUMBER: LER6D30D010-EC6DR4020359035-6LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1253.5	21.6
10°-20°	2808.1	48.3
20°-30°	1405.6	24.2
30°-40°	257.7	4.4
40°-50°	71.1	1.2
50°-60°	16.7	0.3
60°-70°	3.2	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5467.2	94.0
0°-40°	5724.9	98.4
0°-60°	5812.7	99.9
0°-90°	5816.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5816.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	13541	
5°	13424	###
15°	10459	2808
25°	2791	1406
35°	369	258
45°	81	71
55°	17	17
65°	2	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P791450
CATALOG NUMBER: LER6D30D010-EC6DR4020359035-6LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	13541.2
2.5°	13521.4
5°	13424.1
7.5°	13114.0
10°	12543.7
12.5°	11654.5
15°	10459.2
17.5°	8904.8
20°	6935.1
22.5°	4728.1
25°	2790.8
27.5°	1475.3
30°	838.5
32.5°	541.9
35°	368.6
37.5°	263.4
40°	190.6
42.5°	130.5
45°	80.7
47.5°	51.4
50°	35.6
52.5°	25.3
55°	17.4
57.5°	11.1
60°	7.9
62.5°	4.7
65°	2.4
67.5°	1.6
70°	0.8
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)