

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P791502

Luminaire Tested: LER6D30D010-EC6DR4520359035-6LBS1MW

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P791502  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-36)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D30D010-EC6DR4520359035-6LBS1MW  
Description: 6 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 45° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6011.3 lumens  
Efficiency: N/A  
Efficacy: 207.3 lumens/watt  
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.69  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 29  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P791502

CATALOG NUMBER: LER6D30D010-EC6DR4520359035-6LBS1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P791502

CATALOG NUMBER: LER6D30D010-EC6DR4520359035-6LBS1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100		
	1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	98	98	97	95	95	95	95	95	95		
	2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	91	90	90	90	90	90	90		
	3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	89	87	85	85	85	85	85	85		
	4	100	94	89	85	99	93	88	85	91	87	84	89	86	83	87	84	82	81	81	81	81	81	81		
	5	96	89	84	80	95	88	83	80	86	82	79	85	81	79	83	80	78	77	77	77	77	77	77		
	6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	73	73	73	73	73	73		
	7	89	81	75	72	87	80	75	72	79	74	71	78	74	71	77	73	71	69	69	69	69	69	69		
	8	85	77	72	68	84	76	71	68	75	71	68	74	70	67	73	70	67	66	66	66	66	66	66		
	9	82	73	68	65	81	73	68	65	72	68	65	71	67	64	71	67	64	63	63	63	63	63	63		
	10	79	70	65	62	78	70	65	62	69	65	62	68	64	61	68	64	61	60	60	60	60	60	60		

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1160917
5°	1127864
10°	1079063
15°	987562
20°	783481
25°	489144
30°	269599
35°	121058
40°	47681
45°	22467
50°	10658
55°	5562
60°	2732
65°	646
70°	256
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 22467 cd/sqm



TEST NUMBER: P791502

CATALOG NUMBER: LER6D30D010-EC6DR4520359035-6LBS1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	966.2	16.1
10°-20°	2378.0	39.6
20°-30°	1883.1	31.3
30°-40°	627.1	10.4
40°-50°	124.5	2.1
50°-60°	28.2	0.5
60°-70°	4.1	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5227.3	87.0
0°-40°	5854.4	97.4
0°-60°	6007.2	99.9
0°-90°	6011.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6011.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	10625	
5°	10283	966
15°	8731	2378
25°	4057	1883
35°	908	627
45°	145	124
55°	29	28
65°	2	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P791502

CATALOG NUMBER: LER6D30D010-EC6DR4520359035-6LBS1MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	10625.2
2.5°	10555.8
5°	10283.4
7.5°	10058.6
10°	9726.0
12.5°	9283.0
15°	8730.6
17.5°	7900.0
20°	6738.3
22.5°	5354.4
25°	4057.4
27.5°	2970.9
30°	2136.9
32.5°	1453.3
35°	907.6
37.5°	538.2
40°	334.3
42.5°	219.8
45°	145.4
47.5°	93.6
50°	62.7
52.5°	41.8
55°	29.2
57.5°	19.2
60°	12.5
62.5°	6.7
65°	2.5
67.5°	0.8
70°	0.8
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)