

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P790480

Luminaire Tested: LER6D20D010-EC6DR6020359030-6LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P790480
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D20D010-EC6DR6020359030-6LBDP1H
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3356.5 lumens
Efficiency: N/A
Efficacy: 145.3 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 23.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P790480
CATALOG NUMBER: LER6D20D010-EC6DR6020359030-6LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P790480

CATALOG NUMBER: LER6D20D010-EC6DR6020359030-6LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93																
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86			86																
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80			80																
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75			75																
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			70																
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66			66																
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62			62																
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59			59																
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			55																
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53			53																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	435557
5°	446258
10°	451651
15°	430256
20°	379363
25°	306839
30°	207551
35°	103999
40°	16873
45°	16518
50°	16845
55°	17106
60°	17569
65°	17968
70°	18401
75°	18617
80°	17932
85°	14918

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 18617 cd/sqm



TEST NUMBER: P790480

CATALOG NUMBER: LER6D20D010-EC6DR6020359030-6LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	388.9	11.6
10°-20°	1052.1	31.3
20°-30°	1132.0	33.7
30°-40°	492.1	14.7
40°-50°	82.6	2.5
50°-60°	80.4	2.4
60°-70°	68.7	2.0
70°-80°	46.0	1.4
80°-90°	13.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2573.0	76.7
0°-40°	3065.1	91.3
0°-60°	3228.1	96.2
0°-90°	3356.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3356.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3986	
5°	4069	389
15°	3804	1052
25°	2545	1132
35°	780	492
45°	107	83
55°	90	80
65°	70	69
75°	44	46
85°	12	14
90°	0	



TEST NUMBER: P790480

CATALOG NUMBER: LER6D20D010-EC6DR6020359030-6LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	3986.4
2.5°	4098.4
5°	4068.8
7.5°	4078.2
10°	4070.9
12.5°	3986.9
15°	3803.7
17.5°	3557.8
20°	3262.7
22.5°	2946.7
25°	2545.2
27.5°	2035.7
30°	1645.1
32.5°	1267.9
35°	779.7
37.5°	333.6
40°	118.3
42.5°	108.9
45°	106.9
47.5°	103.2
50°	99.1
52.5°	94.4
55°	89.8
57.5°	85.1
60°	80.4
62.5°	75.2
65°	69.5
67.5°	63.8
70°	57.6
72.5°	50.8
75°	44.1
77.5°	36.3
80°	28.5
82.5°	20.2
85°	11.9
87.5°	4.2
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)