

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P790495

Luminaire Tested: LER6D20D010-EC6DR6020359040-6LBDP1B

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P790495  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D20D010-EC6DR6020359040-6LBDP1B  
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 60° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2867.6 lumens  
Efficiency: N/A  
Efficacy: 124.1 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 23.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P790495  
CATALOG NUMBER: LER6D20D010-EC6DR6020359040-6LBDP1B

### Luminous Intensity Polar Plot





TEST NUMBER: P790495

CATALOG NUMBER: LER6D20D010-EC6DR6020359040-6LBDP1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	372098
5°	381241
10°	385849
15°	367579
20°	324087
25°	262125
30°	177310
35°	88846
40°	14420
45°	14107
50°	14397
55°	14611
60°	15012
65°	15357
70°	15717
75°	15915
80°	15353
85°	12787

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 75°  
 Luminance: 15915 cd/sqm



TEST NUMBER: P790495

CATALOG NUMBER: LER6D20D010-EC6DR6020359040-6LBDP1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	332.2	11.6
10°-20°	898.8	31.3
20°-30°	967.1	33.7
30°-40°	420.4	14.7
40°-50°	70.6	2.5
50°-60°	68.7	2.4
60°-70°	58.7	2.0
70°-80°	39.3	1.4
80°-90°	11.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2198.1	76.7
0°-40°	2618.5	91.3
0°-60°	2757.8	96.2
0°-90°	2867.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2867.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3406	
5°	3476	332
15°	3250	899
25°	2174	967
35°	666	420
45°	91	71
55°	77	69
65°	59	59
75°	38	39
85°	10	12
90°	0	



TEST NUMBER: P790495

CATALOG NUMBER: LER6D20D010-EC6DR6020359040-6LBDP1B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3405.6
2.5°	3501.3
5°	3476.0
7.5°	3484.0
10°	3477.8
12.5°	3406.0
15°	3249.6
17.5°	3039.5
20°	2787.3
22.5°	2517.4
25°	2174.3
27.5°	1739.1
30°	1405.4
32.5°	1083.2
35°	666.1
37.5°	285.0
40°	101.1
42.5°	93.1
45°	91.3
47.5°	88.2
50°	84.7
52.5°	80.7
55°	76.7
57.5°	72.7
60°	68.7
62.5°	64.3
65°	59.4
67.5°	54.5
70°	49.2
72.5°	43.4
75°	37.7
77.5°	31.0
80°	24.4
82.5°	17.3
85°	10.2
87.5°	3.5
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)