

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P791615

Luminaire Tested: LER6D30D010-EC6DR6020359024-6LBDP1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P791615
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D30D010-EC6DR6020359024-6LBDP1B
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3832.3 lumens
Efficiency: N/A
Efficacy: 132.1 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 29
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P791615
CATALOG NUMBER: LER6D30D010-EC6DR6020359024-6LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P791615

CATALOG NUMBER: LER6D30D010-EC6DR6020359024-6LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	497289
5°	509521
10°	515678
15°	491247
20°	433128
25°	350323
30°	236973
35°	118751
40°	19255
45°	18851
50°	19225
55°	19525
60°	20060
65°	20528
70°	20988
75°	21234
80°	20512
85°	17049

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 21234 cd/sqm



TEST NUMBER: P791615

CATALOG NUMBER: LER6D30D010-EC6DR6020359024-6LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	444.0	11.6
10°-20°	1201.3	31.3
20°-30°	1292.5	33.7
30°-40°	561.8	14.7
40°-50°	94.4	2.5
50°-60°	91.7	2.4
60°-70°	78.5	2.0
70°-80°	52.5	1.4
80°-90°	15.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2937.8	76.7
0°-40°	3499.6	91.3
0°-60°	3685.7	96.2
0°-90°	3832.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3832.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4551	
5°	4646	444
15°	4343	1201
25°	2906	1292
35°	890	562
45°	122	94
55°	102	92
65°	79	78
75°	50	52
85°	14	16
90°	0	



TEST NUMBER: P791615

CATALOG NUMBER: LER6D30D010-EC6DR6020359024-6LBDP1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	4551.4
2.5°	4679.4
5°	4645.6
7.5°	4656.3
10°	4648.0
12.5°	4552.0
15°	4342.9
17.5°	4062.2
20°	3725.1
22.5°	3364.4
25°	2905.9
27.5°	2324.3
30°	1878.3
32.5°	1447.6
35°	890.3
37.5°	380.9
40°	135.0
42.5°	124.4
45°	122.0
47.5°	117.9
50°	113.1
52.5°	107.8
55°	102.5
57.5°	97.1
60°	91.8
62.5°	85.9
65°	79.4
67.5°	72.9
70°	65.7
72.5°	58.0
75°	50.3
77.5°	41.5
80°	32.6
82.5°	23.1
85°	13.6
87.5°	4.7
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)