

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P791641

Luminaire Tested: LER6D30D010-EC6DR6020359035-6LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P791641
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D30D010-EC6DR6020359035-6LBDDP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6183.3 lumens
Efficiency: N/A
Efficacy: 213.2 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 29
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P791641
CATALOG NUMBER: LER6D30D010-EC6DR6020359035-6LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P791641

CATALOG NUMBER: LER6D30D010-EC6DR6020359035-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93																
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86			86																
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80			80																
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75			75																
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			70																
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66			66																
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62			62																
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59			59																
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			55																
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53			53																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	802345
5°	822081
10°	832008
15°	792597
20°	698823
25°	565226
30°	382326
35°	191591
40°	31079
45°	30425
50°	31021
55°	31488
60°	32363
65°	33118
70°	33894
75°	34279
80°	33096
85°	27580

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 34279 cd/sqm



TEST NUMBER: P791641

CATALOG NUMBER: LER6D30D010-EC6DR6020359035-6LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	716.4	11.6
10°-20°	1938.2	31.3
20°-30°	2085.3	33.7
30°-40°	906.5	14.7
40°-50°	152.3	2.5
50°-60°	148.0	2.4
60°-70°	126.6	2.0
70°-80°	84.7	1.4
80°-90°	25.3	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4739.9	76.7
0°-40°	5646.3	91.3
0°-60°	5946.6	96.2
0°-90°	6183.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6183.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7343	
5°	7495	716
15°	7007	1938
25°	4688	2085
35°	1436	906
45°	197	152
55°	165	148
65°	128	127
75°	81	85
85°	22	25
90°	0	



TEST NUMBER: P791641

CATALOG NUMBER: LER6D30D010-EC6DR6020359035-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	7343.4
2.5°	7549.8
5°	7495.4
7.5°	7512.6
10°	7499.2
12.5°	7344.4
15°	7007.0
17.5°	6554.0
20°	6010.2
22.5°	5428.2
25°	4688.5
27.5°	3750.1
30°	3030.4
32.5°	2335.7
35°	1436.4
37.5°	614.5
40°	217.9
42.5°	200.7
45°	196.9
47.5°	190.2
50°	182.5
52.5°	173.9
55°	165.3
57.5°	156.7
60°	148.1
62.5°	138.6
65°	128.1
67.5°	117.5
70°	106.1
72.5°	93.7
75°	81.2
77.5°	66.9
80°	52.6
82.5°	37.3
85°	22.0
87.5°	7.6
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)