

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P790527

Luminaire Tested: LER6D20D010-EC6DR6520359030-6LBDP1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P790527
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D20D010-EC6DR6520359030-6LBDDP1B
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2184.7 lumens
Efficiency: N/A
Efficacy: 94.6 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 23.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P790527
CATALOG NUMBER: LER6D20D010-EC6DR6520359030-6LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P790527

CATALOG NUMBER: LER6D20D010-EC6DR6520359030-6LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87																			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80																			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69																			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65																			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60																			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57																			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53																			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	235020
5°	235205
10°	243494
15°	243899
20°	224546
25°	191322
30°	146463
35°	103478
40°	61074
45°	24800
50°	8992
55°	5010
60°	2863
65°	1577
70°	1661
75°	1309
80°	1321
85°	1128

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 24800 cd/sqm



TEST NUMBER: P790527

CATALOG NUMBER: LER6D20D010-EC6DR6520359030-6LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	207.1	9.5
10°-20°	597.4	27.3
20°-30°	716.8	32.8
30°-40°	481.7	22.0
40°-50°	144.2	6.6
50°-60°	25.5	1.2
60°-70°	7.2	0.3
70°-80°	3.6	0.2
80°-90°	1.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1521.4	69.6
0°-40°	2003.1	91.7
0°-60°	2172.8	99.5
0°-90°	2184.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2184.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2151	
5°	2144	207
15°	2156	597
25°	1587	717
35°	776	482
45°	160	144
55°	26	25
65°	6	7
75°	3	4
85°	1	1
90°	0	



TEST NUMBER: P790527

CATALOG NUMBER: LER6D20D010-EC6DR6520359030-6LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	2151.0
2.5°	2160.1
5°	2144.5
7.5°	2176.9
10°	2194.7
12.5°	2190.4
15°	2156.2
17.5°	2072.4
20°	1931.2
22.5°	1764.9
25°	1587.0
27.5°	1386.2
30°	1160.9
32.5°	956.7
35°	775.8
37.5°	597.0
40°	428.2
42.5°	279.7
45°	160.5
47.5°	85.0
50°	52.9
52.5°	36.7
55°	26.3
57.5°	19.0
60°	13.1
62.5°	8.6
65°	6.1
67.5°	5.5
70°	5.2
72.5°	4.0
75°	3.1
77.5°	2.8
80°	2.1
82.5°	1.5
85°	0.9
87.5°	0.6
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)