

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P791684

Luminaire Tested: LER6D30D010-EC6DR6520359030-6LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P791684
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D30D010-EC6DR6520359030-6LBS1H
Description: 6 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5130.7 lumens
Efficiency: N/A
Efficacy: 176.9 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 29
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P791684

CATALOG NUMBER: LER6D30D010-EC6DR6520359030-6LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P791684

CATALOG NUMBER: LER6D30D010-EC6DR6520359030-6LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93			93																
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85			85																
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78			78																
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72			72																
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66			66																
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61			61																
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56			56																
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			52																
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49			49																
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46			46																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	272074
5°	271384
10°	271154
15°	262795
20°	239242
25°	208488
30°	173399
35°	137398
40°	99166
45°	62649
50°	32655
55°	17361
60°	9111
65°	5016
70°	2100
75°	2324
80°	1614
85°	1407

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 62649 cd/sqm



TEST NUMBER: P791684

CATALOG NUMBER: LER6D30D010-EC6DR6520359030-6LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	440.5	8.6
10°-20°	1206.4	23.5
20°-30°	1474.6	28.7
30°-40°	1196.5	23.3
40°-50°	596.2	11.6
50°-60°	166.3	3.2
60°-70°	37.8	0.7
70°-80°	9.8	0.2
80°-90°	2.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3121.5	60.8
0°-40°	4318.0	84.2
0°-60°	5080.5	99.0
0°-90°	5130.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5130.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4658	
5°	4629	441
15°	4346	1206
25°	3235	1475
35°	1927	1196
45°	758	596
55°	170	166
65°	36	38
75°	10	10
85°	2	3
90°	0	



TEST NUMBER: P791684

CATALOG NUMBER: LER6D30D010-EC6DR6520359030-6LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	4658.5
2.5°	4655.1
5°	4629.0
7.5°	4614.0
10°	4572.2
12.5°	4487.3
15°	4346.3
17.5°	4125.9
20°	3849.3
22.5°	3550.9
25°	3235.3
27.5°	2897.8
30°	2571.2
32.5°	2248.8
35°	1927.1
37.5°	1606.0
40°	1300.7
42.5°	1014.5
45°	758.5
47.5°	528.5
50°	359.4
52.5°	247.8
55°	170.5
57.5°	115.0
60°	78.0
62.5°	54.1
65°	36.3
67.5°	18.5
70°	12.3
72.5°	11.6
75°	10.3
77.5°	6.8
80°	4.8
82.5°	3.4
85°	2.1
87.5°	1.4
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)