

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P790550

Luminaire Tested: LER6D20D010-EC6DR6520359040-6LBS1MW

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P790550  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D20D010-EC6DR6520359040-6LBS1MW  
Description: 6 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3182.5 lumens  
Efficiency: N/A  
Efficacy: 137.8 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96  
Luminous Opening: Circular (Dia: 0.48' x H: 0')  
CIE Type: Direct


Input Watts (W): 23.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P790550  
CATALOG NUMBER: LER6D20D010-EC6DR6520359040-6LBS1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P790550

CATALOG NUMBER: LER6D20D010-EC6DR6520359040-6LBS1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93																			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78																			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72																			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66																			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61																			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56																			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52																			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49																			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	168764
5°	168341
10°	168194
15°	163011
20°	148401
25°	129321
30°	107558
35°	85230
40°	61511
45°	38861
50°	20253
55°	10763
60°	5653
65°	3109
70°	1298
75°	1444
80°	1009
85°	871

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 38861 cd/sqm



TEST NUMBER: P790550

CATALOG NUMBER: LER6D20D010-EC6DR6520359040-6LBS1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	273.3	8.6
10°-20°	748.3	23.5
20°-30°	914.7	28.7
30°-40°	742.2	23.3
40°-50°	369.8	11.6
50°-60°	103.1	3.2
60°-70°	23.4	0.7
70°-80°	6.1	0.2
80°-90°	1.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1936.3	60.8
0°-40°	2678.4	84.2
0°-60°	3151.4	99.0
0°-90°	3182.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3182.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2890	
5°	2871	273
15°	2696	748
25°	2007	915
35°	1195	742
45°	470	370
55°	106	103
65°	22	23
75°	6	6
85°	1	2
90°	0	



TEST NUMBER: P790550

CATALOG NUMBER: LER6D20D010-EC6DR6520359040-6LBS1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2889.6
2.5°	2887.5
5°	2871.4
7.5°	2862.0
10°	2836.1
12.5°	2783.5
15°	2696.0
17.5°	2559.3
20°	2387.7
22.5°	2202.6
25°	2006.8
27.5°	1797.5
30°	1594.9
32.5°	1394.9
35°	1195.4
37.5°	996.2
40°	806.8
42.5°	629.3
45°	470.5
47.5°	327.8
50°	222.9
52.5°	153.7
55°	105.7
57.5°	71.3
60°	48.4
62.5°	33.5
65°	22.5
67.5°	11.5
70°	7.6
72.5°	7.2
75°	6.4
77.5°	4.2
80°	3.0
82.5°	2.1
85°	1.3
87.5°	0.8
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)