

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P791710

Luminaire Tested: LER6D30D010-EC6DR6520359050-6LBS1MW

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P791710  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D30D010-EC6DR6520359050-6LBS1MW  
Description: 6 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5226.7 lumens  
Efficiency: N/A  
Efficacy: 180.2 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96  
Luminous Opening: Circular (Dia: 0.48' x H: 0')  
CIE Type: Direct

Input Watts (W): 29  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P791710

CATALOG NUMBER: LER6D30D010-EC6DR6520359050-6LBS1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P791710

CATALOG NUMBER: LER6D30D010-EC6DR6520359050-6LBS1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93				93															
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85				85															
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78				78															
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72				72															
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66				66															
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61				61															
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56				56															
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52				52															
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49				49															
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46				46															

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	277161
5°	276467
10°	276230
15°	267711
20°	243717
25°	212386
30°	176643
35°	139965
40°	101019
45°	63822
50°	33264
55°	17677
60°	9286
65°	5113
70°	2152
75°	2369
80°	1648
85°	1407

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 63822 cd/sqm



TEST NUMBER: P791710

CATALOG NUMBER: LER6D30D010-EC6DR6520359050-6LBS1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	448.8	8.6
10°-20°	1228.9	23.5
20°-30°	1502.2	28.7
30°-40°	1218.8	23.3
40°-50°	607.4	11.6
50°-60°	169.4	3.2
60°-70°	38.5	0.7
70°-80°	10.1	0.2
80°-90°	2.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3179.9	60.8
0°-40°	4398.8	84.2
0°-60°	5175.5	99.0
0°-90°	5226.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5226.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4746	
5°	4716	449
15°	4428	1229
25°	3296	1502
35°	1963	1219
45°	773	607
55°	174	169
65°	37	39
75°	10	10
85°	2	3
90°	0	



TEST NUMBER: P791710

CATALOG NUMBER: LER6D30D010-EC6DR6520359050-6LBS1MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	4745.6
2.5°	4742.2
5°	4715.7
7.5°	4700.3
10°	4657.8
12.5°	4571.3
15°	4427.6
17.5°	4203.1
20°	3921.3
22.5°	3617.3
25°	3295.8
27.5°	2952.0
30°	2619.3
32.5°	2290.9
35°	1963.1
37.5°	1636.0
40°	1325.0
42.5°	1033.5
45°	772.7
47.5°	538.4
50°	366.1
52.5°	252.4
55°	173.6
57.5°	117.2
60°	79.5
62.5°	55.1
65°	37.0
67.5°	18.8
70°	12.6
72.5°	11.9
75°	10.5
77.5°	7.0
80°	4.9
82.5°	3.5
85°	2.1
87.5°	1.4
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)