

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P790577

Luminaire Tested: LER6D20D010-EC6DR7020359030-6LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P790577
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D20D010-EC6DR7020359030-6LBDDP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3547.5 lumens
Efficiency: N/A
Efficacy: 153.6 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 23.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P790577

CATALOG NUMBER: LER6D20D010-EC6DR7020359030-6LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P790577

CATALOG NUMBER: LER6D20D010-EC6DR7020359030-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	435776
5°	422831
10°	411045
15°	405653
20°	378794
25°	284572
30°	201168
35°	71253
40°	37469
45°	39912
50°	41322
55°	42098
60°	42371
65°	41469
70°	39133
75°	36263
80°	32153
85°	26075

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 42378 cd/sqm



TEST NUMBER: P790577

CATALOG NUMBER: LER6D20D010-EC6DR7020359030-6LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	363.6	10.3
10°-20°	997.4	28.1
20°-30°	1098.5	31.0
30°-40°	419.7	11.8
40°-50°	198.2	5.6
50°-60°	197.0	5.6
60°-70°	157.7	4.4
70°-80°	90.7	2.6
80°-90°	24.6	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2459.6	69.3
0°-40°	2879.3	81.2
0°-60°	3274.5	92.3
0°-90°	3547.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3547.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3988	
5°	3855	364
15°	3586	997
25°	2360	1099
35°	534	420
45°	258	198
55°	221	197
65°	160	158
75°	86	91
85°	21	25
90°	0	



TEST NUMBER: P790577

CATALOG NUMBER: LER6D20D010-EC6DR7020359030-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	3988.4
2.5°	3946.8
5°	3855.2
7.5°	3778.8
10°	3704.9
12.5°	3642.4
15°	3586.2
17.5°	3450.4
20°	3257.8
22.5°	2842.3
25°	2360.5
27.5°	2054.8
30°	1594.5
32.5°	1029.9
35°	534.2
37.5°	288.6
40°	262.7
42.5°	260.8
45°	258.3
47.5°	252.6
50°	243.1
52.5°	232.4
55°	221.0
57.5°	208.4
60°	193.9
62.5°	177.4
65°	160.4
67.5°	141.5
70°	122.5
72.5°	103.6
75°	85.9
77.5°	67.6
80°	51.1
82.5°	36.0
85°	20.8
87.5°	8.2
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)