

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P791744

Luminaire Tested: LER6D30D010-EC6DR7020359040-6LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P791744
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D30D010-EC6DR7020359040-6LBDP1H
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6091.3 lumens
Efficiency: N/A
Efficacy: 210.0 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 29
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P791744
CATALOG NUMBER: LER6D30D010-EC6DR7020359040-6LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P791744

CATALOG NUMBER: LER6D30D010-EC6DR7020359040-6LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	748261
5°	726025
10°	705796
15°	696529
20°	650419
25°	488625
30°	345410
35°	122352
40°	64340
45°	68529
50°	70966
55°	72291
60°	72746
65°	71200
70°	67214
75°	62267
80°	55244
85°	44880

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 72759 cd/sqm



TEST NUMBER: P791744

CATALOG NUMBER: LER6D30D010-EC6DR7020359040-6LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	624.4	10.3
10°-20°	1712.6	28.1
20°-30°	1886.2	31.0
30°-40°	720.7	11.8
40°-50°	340.3	5.6
50°-60°	338.3	5.6
60°-70°	270.9	4.4
70°-80°	155.7	2.6
80°-90°	42.3	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4223.2	69.3
0°-40°	4943.9	81.2
0°-60°	5622.5	92.3
0°-90°	6091.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6091.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6848	
5°	6620	624
15°	6158	1713
25°	4053	1886
35°	917	721
45°	444	340
55°	380	338
65°	275	271
75°	148	156
85°	36	42
90°	0	



TEST NUMBER: P791744

CATALOG NUMBER: LER6D30D010-EC6DR7020359040-6LBDP1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	6848.4
2.5°	6776.9
5°	6619.6
7.5°	6488.4
10°	6361.6
12.5°	6254.2
15°	6157.7
17.5°	5924.6
20°	5593.9
22.5°	4880.4
25°	4053.1
27.5°	3528.3
30°	2737.8
32.5°	1768.5
35°	917.3
37.5°	495.5
40°	451.1
42.5°	447.8
45°	443.5
47.5°	433.7
50°	417.5
52.5°	399.0
55°	379.5
57.5°	357.8
60°	332.9
62.5°	304.7
65°	275.4
67.5°	242.9
70°	210.4
72.5°	177.8
75°	147.5
77.5°	116.0
80°	87.8
82.5°	61.8
85°	35.8
87.5°	14.1
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)