

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P790583

Luminaire Tested: LER6D20D010-EC6DR7020359035-6LBDP1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P790583
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D20D010-EC6DR7020359035-6LBDDP1B
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2075.2 lumens
Efficiency: N/A
Efficacy: 89.8 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 23.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P790583
CATALOG NUMBER: LER6D20D010-EC6DR7020359035-6LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P790583

CATALOG NUMBER: LER6D20D010-EC6DR7020359035-6LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	254916
5°	247346
10°	240443
15°	237293
20°	221581
25°	166464
30°	117673
35°	41682
40°	21922
45°	23348
50°	24171
55°	24630
60°	24780
65°	24250
70°	22905
75°	21192
80°	18813
85°	15294

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 24789 cd/sqm



TEST NUMBER: P790583

CATALOG NUMBER: LER6D20D010-EC6DR7020359035-6LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	212.7	10.3
10°-20°	583.5	28.1
20°-30°	642.6	31.0
30°-40°	245.5	11.8
40°-50°	115.9	5.6
50°-60°	115.2	5.6
60°-70°	92.3	4.4
70°-80°	53.0	2.6
80°-90°	14.4	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1438.8	69.3
0°-40°	1684.3	81.2
0°-60°	1915.5	92.3
0°-90°	2075.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2075.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2333	
5°	2255	213
15°	2098	583
25°	1381	643
35°	312	246
45°	151	116
55°	129	115
65°	94	92
75°	50	53
85°	12	14
90°	0	



TEST NUMBER: P790583

CATALOG NUMBER: LER6D20D010-EC6DR7020359035-6LBDP1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	2333.1
2.5°	2308.7
5°	2255.2
7.5°	2210.5
10°	2167.2
12.5°	2130.7
15°	2097.8
17.5°	2018.4
20°	1905.7
22.5°	1662.6
25°	1380.8
27.5°	1202.0
30°	932.7
32.5°	602.5
35°	312.5
37.5°	168.8
40°	153.7
42.5°	152.6
45°	151.1
47.5°	147.8
50°	142.2
52.5°	135.9
55°	129.3
57.5°	121.9
60°	113.4
62.5°	103.8
65°	93.8
67.5°	82.7
70°	71.7
72.5°	60.6
75°	50.2
77.5°	39.5
80°	29.9
82.5°	21.1
85°	12.2
87.5°	4.8
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)